

BENT NOSE PLIER

Description

Fully tempered chromium vanadium steel. Curved head shape at 40°. Polished finish. Hardness: 63HRC. For right-angle picking and bending of wires and metal parts. Cutting capacity up to 2 mm steel.



Characteristics

| Ref. | EAN | Nose shape | Length of noses mm | Length mm | Weight g | Cutting capacity mm |
|--------|---------------|--------------------------------|-----------------------|--------------|-------------|------------------------|
| 847020 | 3660338076541 | Half-round, long nose, bent | 53 | 160 | 120 | 2 |
| 847021 | 3660338076558 | Half-round, long nose, bent | 78 | 200 | 165 | 2 |