

Han 3A-HSM-L-11 (bottom closed)



Part number	09 20 003 1252
Specification	Han 3A-HSM-L-11 (bottom closed)
HARTING eCatalogue	https://b2b.harting.com/09200031252

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Surface mounted housing
Description of hood/housing	Bottom closed

Version

Size	3 A
Version	Top entry
Cable entry	1x Pg 11
Locking type	Single locking lever
Field of application	Standard Hoods/housings for industrial applications
Pack contents	Please order seal screw separately.

Technical characteristics

Limiting temperature	-40 +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated



Material properties

RAL 7037 (dust grey)
Steel
Zinc plated
compliant with exemption
6(a) / $6(a)$ -I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight
compliant with exemption
50
Not contained
Not contained
Yes
Lead
Yes
Lead Nickel
EN 45545-2 (2020-08)
R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
Approvals	CE
	DNV GL

Commercial data

Packaging size	10
Net weight	85 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140038745
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors