

FILTER FAN AIR FLOW FREE AIR 58 M3 PER H CUT
OUT 125X125 MM 115 V AC RAL 7035 INPUT
POWER 20W DEGREE OF PROTECTION IP 55

Model		
product brand name		SIVACON
Product designation		filter fan
Type of ventilation		ventilation
Fan design / Insertable fan		No
Design of the product / EMC version		No
General technical data		
A-rated sound power level / maximum	dB	42
Active power consumption / Rated value	W	20
Cutout width	mm	125
Cutout height	mm	125
Operating period	h	27 500
Operating temperature / minimum	°C	-10
Cooling capacity / at 35 °C	W	13.1
Rotor speed / at 50 Hz / Rated value	1/min	2 650
Rotor speed / at 60 Hz / Rated value	1/min	3 100
Protection class		
Protection class IP		IP55
Electricity		
Consumed current / minimum	A	0.23
Main circuit		
Operating voltage		
<ul style="list-style-type: none"> with AC / at 50 Hz / Rated value / maximum 	V	115
<ul style="list-style-type: none"> with AC / at 60 Hz / Rated value / maximum 	V	115
Appearance		
Color		RAL 7035
Product details		
Product component / Fan		No
Number		
Number of ventilators		1
Mechanical Design		
Height	mm	148

Width	mm	148
Depth	mm	70
Mounting type		snap-on mounting
Mounting type		No
<ul style="list-style-type: none"> • 19-inch installation • wall mounting 		Yes
Material		plastic

Certificates

Equipment marking		E
<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 • acc. to DIN EN 81346-2 		E

General Product Approval

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR65115LV25>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR65115LV25/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR65115LV25

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015