

SUBITO KT internal precision measuring instrument

For internal toothing



Application:

For measuring the pitch circle diameter of internal toothing with an odd or even number of teeth, with straight or slanted tooth shapes such as involute toothing.

Execution:

- Graduated, interchangeable gauge slides, with female thread for accommodating measuring ball inserts (not included in the scope of delivery)

Delivery:

Device holder with movable probe bolt, replaceable gauge slides, measuring discs, wooden box. **Ball measuring inserts not included***. Probe bolt and gauge slides with female thread for screwing in ball measuring inserts



Art. no.	33572 055
Brand	SCHWENK
Manufacturer Part Number	16300000
Min./max. diameter of measuring range	55-250 mm
Type	KT
Measuring depth	177 mm
Number of measurement heads	1
Number of measuring pins	7
Nominal dimension of spindle	55 mm, 60 mm, 65 mm, 70 mm, 75 mm, 80 mm, 85 mm, 90 mm, 95 mm, 100 mm
Number of measurement discs	3
Measurement disc thickness	1 mm, 2 mm, 3 mm
Gross Weight	1.895 kg
Product Group	338