

Empty housing for sliding-door cabinet, with partition, height 1028 mm

For fitting with shelves and drawers - custom configuration

Application:

For customised fitting with shelves item no. 50051 400-415 and drawer no. 50051 500-545

Execution:

- Stable welded sheet steel structure, equipped with sliding doors and a partition
- Shelves and drawers are height-adjustable in increments of 30 mm
- Doors can be locked simultaneously with a push-and-turn cylinder lock, incl. 2 keys

Advantage:

- The sliding-door cabinets can be used and combined as top-mounted cabinets for two HK drawer cabinets from system 550 S/700 S/800 S (width 722 mm).



| | |
|---------------------------------|-----------------------|
| Art. no. | 50051 900 |
| Brand | HK |
| Manufacturer Part Number | 50051900 |
| Door design | Full-sheet panel |
| Height | 1028 mm |
| Depth | 620 mm |
| Width | 1444 mm |
| With partition wall | Yes |
| Number of folder height | 2 PCS |
| Number of shelves | 0 PCS |
| Number of drawers | 0 PCS |
| Load-carrying capacity | 500 kg |
| Lock type | Cylinder lock |
| Material | Sheet steel |
| Cabinet colour | Light grey RAL 7035 |
| Colour of front | Gentian blue RAL 5010 |
| Surface | Powder-coated |
| Gross Weight | 82.000 kg |
| Product Group | 501 |

EAN

4039247901296