

Safety isolating transformer FL 14/6



Picture shows FL 42/12

Advantages

Minimum size at high output

Low height

Dual input voltage for series or parallel connection

Dual output voltage for series or parallel connection

Permanent corrosion protection, high insulation value and maximum electrical reliability thanks to XtraDenseFill resin encapsulation

Self-extinguishing potting material


Applications

As a mains transformer for adjustment of the voltage and simple electrical isolation.

As an isolating transformer for the safe electrical isolation of the input and output sides. The transformer may be used to set up protective separation as a protective measure in accordance with VDE 0100.

As a safety isolating transformer for the safe electrical isolation of the input and output sides. The transformer is suitable for creating SELV and PELV circuits because of the limit on the output voltage.

Sample application



Standards

Approvals




VDE, UL 5085-1/-2, CSA 22.2 No.66



Safety isolating transformer FL 14/6

Electrical data		Type	FL 14/6
Input			
Rated input voltage			2 x 115 Vac
Rated frequency			50 - 60 Hz
Output			
Rated output voltage			2 x 6 Vac
Rated Power			14 VA
No-load voltage (app. x factor)			1.28
No-load loss (typ.)			1.20 W
Efficiency			74.0 %
Standards			
Classification			Safety isolating transformer
Approvals			
Approvals			cURus, VDE
Environment			
Ambient temperature max.			40 °C
Safety and protection			
Type			Encapsulated
Insulation class			VDE=E, UL=class 105
Protection index			IP 00
Safety class (prepared)			II
Short circuit strength			non-short-circuit proof
Order numbers			
Order Number			FL 14/6

Mechanical data		Type	FL 14/6
Terminal and mounting			
Terminals			Pins for PCB
Measures and weights			
Core type			UI 39/10,2
Weight			0.32 kg



Subject to change.