

SVQB steel boring bar, positive right
for longitudinal and copy turning with VB indexable insert

ATORN[®]

Application

for longitudinal and copy turning with VB indexable insert, 35°

Version

- Precision-made boring bar, **steel**, with internal cooling, type V, attack angle 107.5°, tip angle 35°, clearance angle 5°

Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces



Art. No.	17855 102
ISO name	A20R SVQB R/L 11
Min. bore diameter	25 mm
Shaft diameter	20 mm
Clearance length	20.5 mm
Length	200 mm
Clamping surface height	18 mm
Suitable for indexable inserts	VB.. 1103..
Tool design	Right

EAN-Code

4050293562323