

## 3-jaw tapered rod lathe chuck DURO-T

Hand chuck in acc. with ISO 702-3



### Application:

Optimised for turning applications, which require extremely high clamping forces, maximum concentricity and reliable continuous repeatability.

### Execution:

- Grease nipples with very easy access are located at each jaw position.
- Fast and regular lubrication to ensure a long service life
- For short tapered bayonet fastening, DIN ISO 702-3 (DIN 55027)
- Large through-bore
- Chuck body surface hardened

### Advantage:

- No longer necessary to dismantle the chuck before lubricating the guides.
- With visual jaw locking and jaw quick-change system

### Delivery:

With 1 set of plain jaws and reverse top jaws, 1 spanner, 1 set of stud bolts and collar nuts (for short taper DIN ISO 702-3 (DIN 55027))



<b>Art. no.</b>	<b>22428 256</b>
<b>Brand</b>	RÖHM
<b>Manufacturer Part Number</b>	437551
<b>Outer diameter</b>	200 mm
<b>DIN</b>	55027
<b>ISO</b>	702-3
<b>Taper shank size</b>	5
<b>Min./max. external clamping width</b>	7-207 mm
<b>Min./max. internal clamping width</b>	71-214 mm
<b>Drill hole 2</b>	52 mm
<b>Max. rotation speed</b>	4600
<b>Tapered bolt diameter</b>	82.5 mm
<b>Tension force</b>	114 kN
<b>Max. torque</b>	155 Nm
<b>Gross Weight</b>	17.000 kg
<b>Product Group</b>	202

### EAN

4019208227887