

Pneumatic straight grinder SRD 6-45/2

260 watt



Application:

Universally applicable for fine and coarse work with milling bits of head diameter 3–8 mm.

Execution:

- Environmentally friendly owing to central air discharge
- Air discharge to the rear

Delivery:

Includes collet chuck ZG 4/6 mm and collet chuck key size 9 + 11; in box



Art. no.	75036 045
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150010750
Model	SRD 6-45/2
Valve design	Rotary valve
Max. idle speed	45000 rpm
Power output	260 W
Air consumption	380 l/min
Connection thread	R 1/8 inch
Inner hose diameter	7 mm
Length	182 mm
Diameter of housing	32 mm
Max. clamping diameter	6 mm
Collet chuck diameter	6 mm
Suitable for max. sanding block diameter	10 mm
Max. HM rotating milling cutter diameter	8 mm
Weight	0.31 kg
Gross Weight	0.974 kg
Product Group	748