

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0938263006](#)  
**Status:** **Active**  
**Overview:** [Magnetic Jacks](#)  
**Description:** MXMag Gigabit Ethernet 8 Core Non-PoE Dual-Port RJ45 Connector, 21.40mm Depth, 2.70mm Phy Pin Length, Right-Angle, Inverted Profile, with Shield Tabs, with Green-Yellow LEDs, Standard Temperature, Tray

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 938240001-K (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification 934620001-N (PDF)</a>	

**General**


Product Family	Modular Jacks/Plugs
Series	<a href="#">93826</a>
Component Type	PCB Jack
Depth	21.40mm
Magnetic	Yes
Overview	<a href="#">Magnetic Jacks</a>
Performance Category	1000Mb
Power over Ethernet (PoE)	Non-PoE
Product Name	Magnetic Jack, MXMag, RJ45
UPC	191128275989

**Physical**

Color - Resin	Black
Durability (mating cycles max)	2500
Inverted / Top Latch	Yes
Jack Height	14.10mm
Keying to Mating Part	None
Lightpipes/LEDs	LEDs
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold over Palladium Nickel
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	11.200/g
Orientation	Right Angle (Side Entry)
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Panel Mount	Spring Tabs
Plating min - Mating	0.051µm (Au), 1.016µm (PdNi)
Port Configuration	1x2
Positions / Loaded Contacts	8/8
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	0° to +70°C
Termination Interface: Style	Through Hole
Wire/Cable Type	N/A

**Electrical**

Current - Maximum per Contact	0.5A
Grounding to PCB	Yes
Grounding to Panel	Yes
Shielded	Yes
Voltage - Maximum	125V



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 7(c)-I**

**REACH SVHC**

Not Contained Per - ECHA\_01\_2020 (16 January 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[93826 Series](#)

**Mates With**

IEC 60603 / TIA-1096-A

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification

938240001-K

Product Specification

934620001-N

Sales Drawing

938260003-000, 990250161-000

This document was generated on 08/24/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**