

IE-WLT-BL-AP-CL-EU

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Features of the BasicLine (IE-WL-BL series)

- IEEE 802.11a/b/g/n compliant access point / client
- MIMO technology for data rates up to 300 Mbit/s
- Fast roaming for interruption-free connection switching between access points
- DFS support in the 5 GHz band

Features of the ValueLine (IE-WL-VL series)

- IEEE 802.11a/b/g/n compliant access point / client / bridge
- MIMO technology for data rates up to 300 Mbit/s
- Fast roaming for interruption-free connection switching between access points
- DFS support in the 5 GHz band
- Power supply via PoE to IEEE 802.3af possible
- Integrated DI/DOs for monitoring and alarms

General ordering data

Version	Wireless Access Point/Client, IEEE 802.11 a/b/g/n, EU-Model, IP30, -40 °C...75 °C
Order No.	2536650000
Type	IE-WLT-BL-AP-CL-EU
GTIN (EAN)	4050118548662
Qty.	1 pc(s).

IE-WLT-BL-AP-CL-EU

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	115 mm	Height (inches)	4.528 inch
Width	58 mm	Width (inches)	2.283 inch
Net weight	330 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	75 °C
Humidity	5 to 95 % (non-condensing)		

EMC conformity and approvals

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15B Class B, IEC 61000-4-2 ESD: Contact: 4 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 Ghz: 10 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 1 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 1 kV, IEC 61000-4-6 CS: 3 V/m, IEC 61000-4-8	Safety standard	SELV according to EN 62368-1, UL 60950-1
Shock	according to IEC 60068-2-27	Vibration	according to IEC 60068-2-6
Wireless	EN 301 489-1/17, EN 300 328, EN 301893, TELECOM, FCC ID SLE-WAPN008		

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	75 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Guarantee

Time interval	5 years
---------------	---------

Interfaces

Connector for external antennas	2x RP-SMA female	Console port interface	RS-232 (RJ45 connector)
Function reset button	Restoration of factory settings	LED indicator	PWR, FAULT, STATE, SIGNAL, WLAN, 10/100/1000M (TP-Port)
RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port	Standard antenna	2 dBi omni-directional dual band antenna, RP-SMA (male plug)

Creation date March 10, 2023 8:43:57 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

IE-WLT-BL-AP-CL-EU

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

Technical data

MTBF

MTBF	According to Standard	Telcordia SR-332
	Operating time (hours), min.	749,476 h

Power supply

Connection type	1 removable 4-pin terminal block, 500 V insulation	
Current consumption	0.56 A at 12 V DC, 0.14 A at 48 V DC	
Power consumption	6.96 W	
Reverse polarity protection	Available	
Voltage supply	24 V DC, 2 redundant inputs	
Voltage supply range	Voltage type	DC
	Voltage, min.	12 V
	Voltage, max.	48 V

Technical data

Housing main material	metal	Protection degree	IP30
Type of mounting	DIN rail		

Technology

Standard	IEEE 802.11 a/b/g/n for Wireless LAN, IEEE 802.11i for Wireless Security, IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X), IEEE 802.3ab for 1000BaseT(X)	Supported protocols	Proxy ARP, DNS, HTTP, HTTPS, IP, ICMP, SNMP, TCP, UDP, Radius, SNMP, DHCP, LLDP
----------	--------------------------------------------------------------------------------------------------------------------------------------------------------------	---------------------	---------------------------------------------------------------------------------

WLAN interface

Data security	SSID broadcast enable/disable, Firewall for MAC/IP/protocol/port-based filtering, 64-bit and 128-bit WEP encryption, WPA/WPA2 Personal and Enterprise (IEEE 802.1X/RADIUS, TKIP and AES)	
Operating channels (mid-band)	EU: 2.412 to 2.472 GHz (13 channels); 5.180 to 5.240 GHz (4 channels); 5.260 to 5.320 GHz (4 channels); 5.500 to 5.700 GHz (11 channels)	
Spreading code process and modulation (typical)	DSSS with DBPSK, DQPSK, CCK, OFDM with BPSK, QPSK, 16QAM, 64QAM, 802.11b: CCK at 11/5.5 MBit/s, DQPSK at 2 MBit/s, DBPSK at 1 MBit/s, 802.11a / g: 64QAM at 54/48 MBit/s, 16QAM at 36/24 MBit/s, QPSK at 18/12 MBit/s, BPSK at 9/6 MBit/s, 802.11n: 64QAM at 300 MBit/s to BPSK at 6.5 MBit/s	
Transmission rate	802.11b: 1, 2, 5, 11 MBit/s, 802.11a/g: 6, 9, 12, 18, 24, 36, 48, 54 MBit/s, 802.11n: 6.5 to 300 MBit/s	
Transmission rate WLAN	Standard	IEEE 802.11b
	max.	11 Mbps
	min.	1 Mbps
	Standard	IEEE 802.11a/g
	max.	54 Mbps
	min.	6 Mbps
	Standard	IEEE 802.11n
	max.	300 Mbps
	min.	6.5 Mbps

IE-WLT-BL-AP-CL-EU

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

Technical data

Transmit power	802.11b: type 26±1.5 dBm at 1 MBit/s, type 26±1.5 dBm at 2 MBit/s, type 26±1.5 dBm at 5.5 MBit/s, type 25±1.5 dBm at 11 MBit/s, 802.11g: type 23±1.5 dBm at 6 to 24 MBit/s, type 23±1.5 dBm at 36 MBit/s, type 19±1.5 dBm at 48 MBit/s, type 18±1.5 dBm at 54 MBit/s, 802.11a: type 23±1.5 dBm at 6 bis 24 MBit/s, type 21±1.5 dBm at 36 MBit/s, type 20±1.5 dBm at 48 MBit/s, type 18±1.5 dBm at 54 MBit/s, 802.11n (2.4 GHz): type 23±1.5 dBm at MCS0/8 20 MHz, type 18±1.5 dBm at MCS7/15 20 MHz, type 23±1.5 dBm at MCS0/8 40 MHz, type 17±1.5 dBm at MCS7/15 40 MHz, 802.11n (5 GHz): type 23±1.5 dBm at MCS0/8 20 MHz, type 18±1.5 dBm at MCS7/15 20 MHz, type 23±1.5 dBm at MCS0/8 40 MHz, type 17±1.5 dBm at MCS7/15 40 MHz
Wireless LAN receive sensitivity	802.11b: -93 dBm at 1 MBit/s, -93 dBm at 2 MBit/s, -93 dBm at 5.5 MBit/s, -88 dBm at 11 MBit/s, 802.11g: -88 dBm at 6 MBit/s, -86 dBm at 9 MBit/s, -85 dBm at 12 MBit/s, -85 dBm at 18 MBit/s, -85 dBm at 24 MBit/s, -82 dBm at 36 MBit/s, -78 dBm at 48 MBit/s, -74 dBm at 54 MBit/s, 802.11a: -90 dBm at 6 MBit/s, -88 dBm at 9 MBit/s, -88 dBm at 12 MBit/s, -85 dBm at 18 MBit/s, -81 dBm at 24 MBit/s, -78 dBm at 36 MBit/s, -74 dBm at 48 MBit/s, -72 dBm at 54 MBit/s, 802.11n (2.4 GHz): -70 dBm at MCS7 20 MHz, -69 dBm at MCS15 20 MHz, -67 dBm at MCS7 40 MHz, -67 dBm at MCS15 40 MHz, 802.11n (5 GHz): -69 dBm at MCS7 20 MHz, -71 dBm at MCS15 20 MHz, -63 dBm at MCS7 40 MHz, -68 dBm at MCS15 40 MHz

Classifications

ETIM 6.0	EC000816	ETIM 7.0	EC000816
ETIM 8.0	EC000816	ECLASS 9.0	19-17-02-01
ECLASS 9.1	19-17-02-06	ECLASS 10.0	19-17-05-01
ECLASS 11.0	19-17-05-01	ECLASS 12.0	19-17-05-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E230683

Downloads

Approval/Certificate/Document of Conformity	KC certificate EU Declaration of Conformity UK Declaration of Conformity
Engineering Data	CAD data – STEP
Product Change Notification	Firmware Release Notes Product Change Notification IE-WL-BL-series
Software	Software – WLAN Administration Tool Firmware – Firmware Device description – SNMP private MIB
User Documentation	Hardware Installation Guide Manual 20210702 Security Advisory – Multiple vulnerabilities in Industrial WLAN devices (Update A)
Catalogues	Catalogues in PDF-format

Creation date March 10, 2023 8:43:57 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.