

Steckhülsen isoliert 7,7 mm und 9,5 mm Clips femelles isolés Receptacles insulated


UL-No. E235796

mit Stützhülse

Werkstoff:
MS sn = Messing verzinkt

Temperaturbeständigkeit:
PVC -10°C bis +75°C

Strombelastbarkeit:
0.5 – 1.0 mm²/10A max.
1.5 – 2.5 mm²/15A max.
4.0 – 6.0 mm²/25A max.



avec douille-support

Matière:
MS sn = laiton étamé

Résistant à une température de:
PVC -10°C à +75°C



Intensité admissible:
0.5 – 1.0 mm²/10A max.
1.5 – 2.5 mm²/15A max.
4.0 – 6.0 mm²/25A max.

with extra support-sleeve

Material:
MS sn = tin-plated brass

Temperature range:
PVC -10°C up to +75°C


Current carrying capacity:
0.5 – 1.0 mm²/10A max.
1.5 – 2.5 mm²/15A max.
4.0 – 6.0 mm²/25A max.



PVC									
mm ²	AWG	Größe Grandeur Size	Farbe Couleur Colour	Artikelnummer Numéro d'article Part-No.	L mm	A mm	øD mm	Werkzeuge Outils Toolings	
0.5-1	22-18	7.7 x 0.8		3908	24.5	10.5	1.7	3974n,	
1.5-2.5	16-14	7.7 x 0.8		3909	24.5	10.5	2.3	3983p.1, 3984c, 3984cx, 3984o, 3984ox, 3986c, 3986n, 3986s	

mit Stützhülse

avec douille-support

with extra support-sleeve






PVC									
mm ²	AWG	Größe Grandeur Size	Farbe Couleur Colour	Artikelnummer Numéro d'article Part-No.	L mm	A mm	øD mm	Werkzeuge Outils Toolings	
1.5-2.5	16-14	9.5 x 1.2		3919	26	10.5	2.3	3974n, 3986c,	
4-6	12-10	9.5 x 1.2		3914	28.5	13	3.4	3986n, 3986s	

ohne Stützhülse

sans douille-support

without extra support-sleeve



PVC									
mm ²	AWG	Größe Grandeur Size	Farbe Couleur Colour	Artikelnummer Numéro d'article Part-No.	L mm	A mm	øD mm	Werkzeuge Outils Toolings	
1.5-2.5	16-14	9.5 x 1.2		3919s	26	10.5	2.3	3974n, 3986c,	
4-6	12-10	9.5 x 1.2		3914s	28.5	13	3.4	3986n, 3986s	