



Connectors > Rectangular Connectors > Rectangular Contact Inserts



Contact Type: **Socket**

Contact Insert Pole Configuration: **6**

Termination Method to Wire & Cable: **Crimp Terminal**

Number of Positions: **6**

Sealable: **No**

Features

Product Type Features

Product Type	Insert
Sealable	No

Configuration Features

Number of Positions	6
---------------------	---

Contact Features

Contact Type	Socket
Contact Insert Pole Configuration	6

Termination Features

Termination Method to Wire & Cable	Crimp Terminal
------------------------------------	----------------

Dimensions

Wire Size	18 – 10 AWG, 26 – 14 AWG
-----------	--------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # T1509081100-000
H8A-AG

TE Part # T3100000013-000
REMOV-MM

TE Part # T2020002025-000
CDF-2.5

TE Part # T2040002060-000
CMF-6.0

TE Part # T2080062101-100
HQ-4/2-M

Also in the Series | [HDC HQ](#)



Rectangular Contact Inserts(15)

Customers Also Bought



TE Part #T1220320140-000
H32B-TG-M40



TE Part #2842154-5
10P,2MM,BRK HDR,DRRT,2.8,0.1AU,
TB W/CAP



TE Part #2-2319764-0
E STACK PIANO 10P G SHORT TUBE
PD OFF



TE Part #4-2176379-5
RQ 0805 309R 0.1% 10PPM 5K RL



TE Part #2351450-1
SMINSA SW PPL 1.47N 5A/3A AC 3A
DC SP



TE Part #T0924027845-000
H16BPR-2P-350-FRAME



TE Part #T1420240000-000
H24B-AG-BO



TE Part #T1460100125-000
H10B-SDR-BO-M25



TE Part #T1926222600-000
BK26,22-26



TE Part #T3609500102-000
DLX-50-M

Documents

Product Drawings

[HQ-4/2-F](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_T2080062201-100_B.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_T2080062201-100_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T2080062201-100_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

[HEAVY DUTY CONNECTORS](#)

English

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English