


Grove - Electricity Sensor



The Electricity sensor module is a member of Grove. It is based on the TA12-200 current transformer which can transform the large AC into small amplitude. You can use it to test large alternating current up to 5A.

Get One Now 

[<https://www.seeedstudio.com/Grove-Electricity-Sensor-p-777.html>]

Features

- Grove compatible interface
- Maximum 5A input
- High accuracy
- Small size



Tip

More details about Grove modules please refer to [Grove System](#)

[https://wiki.seeedstudio.com/Grove_System/]

Application Ideas

- Alternating current measurement
- Device condition monitoring

Specification

Key Specification


Items	Min
PCB Size	2.0cm*4.0cm
Interface	2.0mm pitch pin header
IO Structure	SIG,NC,NC,GND
RoHS	YES

Electronic Characteristics


Items	Min	Norm	Max	Unit
Transformation ratio	-	2000:1	-	-
Input Current	0	-	5	A
Output Current	0	-	2.5	mA
Sampling Resistance	-	800	-	Ω
Sampling Voltage	0	-	2	V
Working Frequency	20	-	20K	HZ
Nonlinear scale	-	-	0.2%	-
Phase Shift	-	-	5'	-
Operating Temperature	-55	-	85	$^{\circ}\text{C}$
Dielectric strength	-	6	-	KVAC/1mi



Hardware Overview



Platforms Supported



Caution

The platforms mentioned above as supported is/are an indication of the module's software or theoretical compatibility. We only provide software library or code examples for Arduino platform in most cases. It is not

possible to provide software library / demo code for all possible MCU platforms. Hence, users have to write their own software library.

Getting started

Play with Arduino

The following sketch demonstrates a simple application of measuring the amplitude of the alternating voltage. The SIG pin will output a alternating voltage based on the alternating current being measured. You can measure the value using ADC.

Hardware

- **Step 1.** Prepare the below stuffs:


Seeeduino V4.2



[Get One Now](https://www.seeedstudio.com/Seeeduino-V4.2-p-2517.html)

[<https://www.seeedstudio.com/Seeeduino-V4.2-p-2517.html>]

Base Shield




[Get One Now](https://www.seeedstudio.com/Base-Shield-V2-p-1378.html)

[<https://www.seeedstudio.com/Base-Shield-V2-p-1378.html>]



- **Step 2.** Connect Grove-Electricity_Sensor to port **A0** of Grove-Base Shield.
- **Step 3.** Plug Grove - Base Shield into Seeduino.
- **Step 4.** Connect Seeduino to PC via a USB cable.

**Note**

If we don't have Grove Base Shield, We also can directly connect this module to Seeduino as below.

Seeeduino	Grove-Electricity_Sensor
5V	Red
GND	Black
Not Conencted	White
A0	Yellow

Software

Step 1. Copy the code and flash it into the controller board and upload the code.

```

1  /******
2  // Function: Measure the amplitude current of the a
3  //           the effective current of the sinusoida
4  // Hardware: Grove - Electricity Sensor
5  // Date:    Jan 19,2013
6  // by www.seeedstudio.com
7  #define ELECTRICITY_SENSOR A0 // Analog input pin th
8
9  float amplitude_current;           //amplitude c
10 float effective_value;             //effective current
11
12 void setup()
13 {
14     Serial.begin(9600);
15     pins_init();
16 }
17 void loop()
18 {
19     int sensor_max;
20     sensor_max = getMaxValue();
21     Serial.print("sensor_max = ");

```



```

22     Serial.println(sensor_max);
23     //the VCC on the Grove interface of the sensor is 5V
24     amplitude_current=(float)sensor_max/1024*5/800*2000000;
25     effective_value=amplitude_current/1.414;//minimum effective value
26     //Only for sinusoidal alternating current
27     Serial.println("The amplitude of the current is:");
28     Serial.println(amplitude_current,1);//Only one decimal place
29     Serial.println("The effective value of the current is:");
30     Serial.println(effective_value,1);
31 }
32 void pins_init()
33 {
34     pinMode(ELECTRICITY_SENSOR, INPUT);
35 }
36 /*Function: Sample for 1000ms and get the maximum value*/
37 int getMaxValue()
38 {
39     int sensorValue;           //value read from the sensor
40     int sensorMax = 0;
41     uint32_t start_time = millis();
42     while((millis()-start_time) < 1000)//sample for 1000ms
43     {
44         sensorValue = analogRead(ELECTRICITY_SENSOR);
45         if (sensorValue > sensorMax)
46         {
47             /*record the maximum sensor value*/
48             sensorMax = sensorValue;
49         }
50     }
51     return sensorMax;
52 }

```



Note

The minimum effective current that can be sensed by the code can be calculated using the equation below.

$$\text{minimum_current} = 1/1024 * 5/800 * 2000000 / 1.414 = 8.6(\text{mA}).$$

- **Step 2.** Open the serial monitor, The results is as follows:

```

COM21
sensor_max = 0
The amplitude of the current is(in mA)
0.0
The effective value of the current is(in mA)
0.0
sensor_max = 0
The amplitude of the current is(in mA)
0.0
The effective value of the current is(in mA)
0.0
sensor_max = 0
The amplitude of the current is(in mA)
0.0
The effective value of the current is(in mA)
0.0

```

With Raspberry Pi

Hardware

- **Step 1.** Prepare the below stuffs:

Raspberry pi



[Get One Now](https://www.seeedstudio.com/Raspberry-Pi-3-Model-B-p-2625.html)

[<https://www.seeedstudio.com/Raspberry-Pi-3-Model-B-p-2625.html>]


GrovePi_Plus



[Get One Now](https://www.seeedstudio.com/GrovePi-Plus-p-2241.html)

[<https://www.seeedstudio.com/GrovePi-Plus-p-2241.html>]

- **Step 2.** Plug the GrovePi_Plus into Raspberry.
- **Step 3.** Connect Grove-Electricity_Sensor to **A0** port of GrovePi_Plus.
- **Step 4.** Connect the Raspberry to PC through USB cable.



Software

- **Step 1.** Follow [Setting Software](https://www.dexterindustries.com/GrovePi/get-started-with-the-grovepi/setting-software/) [https://www.dexterindustries.com/GrovePi/get-started-with-the-grovepi/setting-software/] to configure the development environment.
- **Step 2.** Git clone the Github repository.

```
1 cd ~
```



```
2 git clone https://github.com/DexterInd/GrovePi.git
```

- **Step 3.** Execute below commands to use this sensor


```
1 cd ~/GrovePi/Software/Python
2 python grove_electricity_sensor.py
```

Here is the code of example:

```
1 #!/usr/bin/env python
2 #
3 # GrovePi Example for using the Grove Electricity Sensor
4 #
5 # The GrovePi connects the Raspberry Pi and Grove sensor.
6 #
7 # Have a question about this example? Ask on the forums
8 #
9 '''
10 ## License
11 The MIT License (MIT)
12 GrovePi for the Raspberry Pi: an open source platform for
13 Copyright (C) 2017 Dexter Industries
14 Permission is hereby granted, free of charge, to any person
15 of this software and associated documentation files (the
16 "Software"), to use, copy, modify, merge, publish, distribute,
17 sublicense, and to permit persons to whom the Software is
18 furnished to do so, subject to the following conditions:
19 The above copyright notice and this permission notice shall
20 be included in all copies or substantial portions of the
21 Software.
22 THE SOFTWARE IS PROVIDED "AS IS", WITHOUT WARRANTY OF ANY
23 KIND, INCLUDING BUT NOT LIMITED TO THE WARRANTIES OF
24 MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE AND
25 NONINFRINGEMENT. IN NO EVENT SHALL THE AUTHORS OR COPYRIGHT
26 HOLDERS BE LIABLE FOR ANY CLAIM, DAMAGES OR OTHER
27 LIABILITY, WHETHER IN AN ACTION OF CONTRACT, TORT OR OTHERWISE,
28 ARISING OUT OF OR IN CONNECTION WITH THE SOFTWARE OR THE USE OR
29 DISPOSITION OF THE SOFTWARE.
```

```
29 '''
30
31 import time
32 import grovepi
33
34 # Connect the Grove Electricity Sensor to analog port A0
35 # SIG,NC,NC,GND
36 sensor = 0
37
38 grovepi.pinMode(sensor,"INPUT")
39
40 # Vcc of the grove interface is normally 5v
41 grove_vcc = 5
42
43 while True:
44     try:
45         # Get sensor value
46         sensor_value = grovepi.analogRead(sensor)
47
48         # Calculate amplitude current (mA)
49         amplitude_current = (float)(sensor_value / 1024 * |
50
51         # Calculate effective value (mA)
52         effective_value = amplitude_current / 1.414
53
54         # minimum_current = 1 / 1024 * grove_vcc / 800 * 2|
55         # Only for sinusoidal alternating current
56
57         print("sensor_value", sensor_value)
58         print("The amplitude of the current is", amplitude_
59         print("The effective value of the current is", effi
60         time.sleep(1)
61
62     except IOError:
63         print ("Error")
```

Here is the result.



```
pi@raspberrypi: ~/Desktop/GrovePi/Software/Python
pi@raspberrypi:~/Desktop/GrovePi/Software/Python $ python grove_electricity_sensor.py
('sensor_value', 0)
('The amplitude of the current is', 0.0, 'mA')
('The effective value of the current is', 0.0, 'mA')
('sensor_value', 0)
('The amplitude of the current is', 0.0, 'mA')
('The effective value of the current is', 0.0, 'mA')
('sensor_value', 0)
('The amplitude of the current is', 0.0, 'mA')
('The effective value of the current is', 0.0, 'mA')
('sensor_value', 0)
('The amplitude of the current is', 0.0, 'mA')
('The effective value of the current is', 0.0, 'mA')
('sensor_value', 0)
('The amplitude of the current is', 0.0, 'mA')
('The effective value of the current is', 0.0, 'mA')
('sensor_value', 0)
('The amplitude of the current is', 0.0, 'mA')
('The effective value of the current is', 0.0, 'mA')
```

Schematic Online Viewer



Resources

- **[Eagle]** [Grove -Electricity Sensor Eagle File](https://files.seeedstudio.com/wiki/Grove-Electricity_Sensor/res/Electricity_sensor_v1.0_eagle_files.zip)
[https://files.seeedstudio.com/wiki/Grove-Electricity_Sensor/res/Electricity_sensor_v1.0_eagle_files.zip]
- **[PDF]** [Schematic in PDF](https://files.seeedstudio.com/wiki/Grove-Electricity_Sensor/res/Electricity_sensor_sch.pdf)
[https://files.seeedstudio.com/wiki/Grove-Electricity_Sensor/res/Electricity_sensor_sch.pdf]

Tech Support

Please submit any technical issue into our [forum](https://forum.seeedstudio.com/)
[<https://forum.seeedstudio.com/>].



[https://www.seeedstudio.com/act-4.html?utm_source=wiki&utm_medium=wikibanner&utm_campaign=newproducts]