

RES80F12



Rev. 0

CHARACTERISTICS:

Rated Voltage:	250VAC max
Rated Current at Ambient:	12A @ 40°C
Operating Frequency:	DC-400HZ
Climatic Class (IEC60068-1):	25/100/21
Temperature Range:	-25°C to +100°C
Over load Current:	1.5 x Rated Ct. for 1 Min
Operational Leakage current : (at 230VAC/50Hz and Total C +/-20%)	0.734 mA max
Worst case Leakage current : (N interrupted and Total C +/-20%)	<1.101 mA max
DCR @ 25°C (+/-25%) :	60 mΩ
Test Voltage (100%) for 2 sec:-	L-N: 1100VDC
	L-GND: 3000VDC
Ingress Protection:	IP 20
Weight (Approximate):	650 gr
FILTER PARAMETERS:	Total Inductance (L-L'+N-N') @10KHz:
	3.30mH +50%,-30%
	Total Capacitance (L-L/L-N) @1KHz:
	2μF +/- -20%
	Total Capacitance (L/N-PE) @1KHz:
	9.4nF +/- -20%
	Total Resistance (L-L/L-N):
	0.22MΩ +/- -10%
	Total Resistance (L/N-GND):

APPROVALS:REACH
RoHS
ULAPPROVED
BY
AJAY

Date: 10-04-2014


CIRCUIT DIAGRAM:**MECHANICAL DIMENSION (mm):****Note:**Housing matl. Fe with Ni Plated
Fast-On Terminal (6.3 x 0.8mm)
Connections

TOLERANCE: +/-1.0 mm




ROXBURGH EMC
FILTER INSERTION LOSS CHARACTERISTICS
CISPR 17 - 50 OHM METHOD

RES80F12



COMMON MODE



DIFFERENTIAL MODE

