

## Section 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**Product name:** PLASTIC EPOXY STICK

**Product code:** 89025

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

**Use of substance / mixture:** PC1: Adhesives, sealants.

### 1.3. Details of the supplier of the safety data sheet

**Company name:** Jenolite UK Ltd  
Chater Lea Buildings  
Letchworth  
Hertfordshire  
SG6 1WT  
**Tel:** 01462 480764  
**Email:** [Sales@Jenolite.net](mailto:Sales@Jenolite.net)

### 1.4. Emergency telephone number

**Emergency tel:** 01462 480764  
(office hours only)

## Section 2: Hazards identification

### 2.1. Classification of the substance or mixture

**Classification under CLP:** Skin Sens. 1: H317; -: EUH205

**Most important adverse effects:** May cause an allergic skin reaction. Contains epoxy constituents. May produce an allergic reaction.

### 2.2. Label elements

**Label elements:**

**Hazard statements:** H317: May cause an allergic skin reaction.  
EUH205: Contains epoxy constituents. May produce an allergic reaction.

**Hazard pictograms:** GHS07: Exclamation mark



**Signal words:** Warning

**Precautionary statements:** P261: Avoid breathing dust/fumes/gas/mist/vapours/spray.  
P272: Contaminated work clothing should not be allowed out of the workplace.  
P280: Wear protective gloves.

# SAFETY DATA SHEET

## PLASTIC EPOXY STICK

Page: 2

P302+P352: IF ON SKIN: Wash with plenty of water.

P321: Specific treatment (see information on this label)

P333+P313: If skin irritation or rash occurs: Get medical advice/attention.

P501: Dispose of contents/container to comply with local, national and international regulations.

**Haz. ingredients (label):** TALC; 2,4,6-TRIS(DIMETHYLAMINOMETHYL)PHENOL; BISPHENOL A-(EPICHLORHYDRIN) {REACTION PRODUCT}

### 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

TALC

EINECS	CAS	PBT / WEL	CLP Classification	Percent
238-877-9	14807-96-6	Substance with a Community workplace exposure limit.	-	30-50%

2,4,6-TRIS(DIMETHYLAMINOMETHYL)PHENOL

202-013-9	90-72-2	-	Acute Tox. 4: H302; Eye Irrit. 2: H319; Skin Irrit. 2: H315	1-2.9%
-----------	---------	---	---	--------

BISPHENOL A-(EPICHLORHYDRIN) {REACTION PRODUCT} - REACH registered number(s): 01-2119456619-26

500-033-5	25068-38-6	-	Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317; Aquatic Chronic 2: H411	1-2.9%
-----------	------------	---	--	--------

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water. Consult a doctor.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** Exposure may cause coughing or wheezing.

[cont...]

# SAFETY DATA SHEET

## PLASTIC EPOXY STICK

Page: 3

**Delayed / immediate effects:** Delayed effects can be expected after long-term exposure.

### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Not applicable.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Do not attempt to take action without suitable protective clothing - see section 8 of SDS.  
Do not create dust.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Transfer to a closable, labelled salvage container for disposal by an appropriate method.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance. Avoid the formation or spread of dust in the air.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed.

### 7.3. Specific end use(s)

**Specific end use(s):** No data available.

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

[cont...]

# SAFETY DATA SHEET

PLASTIC EPOXY STICK

Page: 4

**Hazardous ingredients:**

**TALC**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	-	-	1 mg/m <sup>3</sup>	-

## DNEL/PNEC Values

**DNEL / PNEC** No data available.

## 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area.

**Respiratory protection:** Self-contained breathing apparatus must be available in case of emergency. Respiratory protective device with particle filter.

**Hand protection:** Protective gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Solid

**Colour:** Pale blue

**Odour:** Characteristic odour

**Solubility in water:** Insoluble

**Flash point°C:** >93

**Vapour pressure:** <500Pa @ 20degC

**Relative density:** 1.8

### 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions. Decomposition may occur on exposure to conditions or materials listed below.

[cont...]

# SAFETY DATA SHEET

PLASTIC EPOXY STICK

Page: 5

## 10.4. Conditions to avoid

**Conditions to avoid:** Heat.

## 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong acids.

## 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

**Hazardous ingredients:**

#### 2,4,6-TRIS(DIMETHYLAMINOMETHYL)PHENOL

ORL	RAT	LD50	1200	mg/kg
SKN	RAT	LD50	1280	mg/kg

#### BISPHENOL A-(EPICHLORHYDRIN) {REACTION PRODUCT}

ORL	MUS	LD50	15600	mg/kg
ORL	RAT	LD50	11400	mg/kg
SKN	RBT	LD50	>20	ml/kg

**Relevant hazards for product:**

Hazard	Route	Basis
Respiratory/skin sensitisation	DRM	Hazardous: calculated

### Symptoms / routes of exposure

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** Exposure may cause coughing or wheezing.

**Delayed / immediate effects:** Delayed effects can be expected after long-term exposure.

## Section 12: Ecological information

### 12.1. Toxicity

**Ecotoxicity values:** No data available.

### 12.2. Persistence and degradability

**Persistence and degradability:** Biodegradable.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No bioaccumulation potential.

[cont...]

# SAFETY DATA SHEET

## PLASTIC EPOXY STICK

Page: 6

### 12.4. Mobility in soil

**Mobility:** Insoluble in water.

### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

### 12.6. Other adverse effects

**Other adverse effects:** Negligible ecotoxicity.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**Waste code number:** 08 04 09

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

**Transport class:** This product does not require a classification for transport.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**Specific regulations:** Not applicable.

### 15.2. Chemical Safety Assessment

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

\* indicates text in the SDS which has changed since the last revision.

**Phrases used in s.2 and s.3:** EUH205: Contains epoxy constituents. May produce an allergic reaction.

H302: Harmful if swallowed.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.

[final page]