

HSSE PM roughing and finishing cutter

4 cutters, TiAlN-coated

ATORN®



Application

Roughing cutter for universal machining.

Version

- HSSE PM
- HRF - fine roughing and finishing teeth
- Centre cutting
- Straight shank according to DIN 1835 B
- TiAlN-coating for maximum service life
- Also for dry milling with compressed air
- Twist angle 30°

| Application | Steel (N/mm ²) | | | Stainless steel | | Alu | | Brass | | Bronze | | Plas-tics | Graphite G(C)FK | GG(G) GJMW | Titan-alloy | Nickel-alloy | Super-alloy | Hard mat. | |
|-------------|----------------------------|-------|-------|-----------------|---------|-------|------|-------|------|--------|------|-----------|-----------------|------------|-------------|--------------|-------------|-----------|---------|
| | <700 | <1000 | <1300 | marten. | austen. | short | long | short | long | short | long | | | | | | | <55 HRC | <65 HRC |
| | 78 | 51 | 35 | 43 | 43 | 130 | | | 70 | | 85 | | | 75 | 23 | 23 | 20 | | |

| | |
|---------------------------------------|-------------------|
| Art. No. | 15312 250 |
| Cutting material | HSSE-PM |
| Surface | TiAlN |
| Type | HF |
| Number of cutting edges | 5 PCS |
| Twist angle | 30° |
| Edge protection chamfer length | 0.2 mm |
| Tool holding device | HB parallel shank |
| Overall length | Normal |
| Cutting edge diameter | 25 mm |
| Cutting edge length | 45 mm |
| Length | 121 mm |
| Shaft diameter | 25 mm |
| fz steel 700 | 0.14 mm |

EAN-Code

4050293387810