

I/O extension module - NLC-IO-2AI-2AO-01 - 2701040

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



I/O extension module for use with Nanoline base unit. Equipped with 2 analog input (0...10 V DC, -10...+10 V DC, 0/4...20 mA) and 2 analog output (0...10 V DC, 0/4...20 mA) channels. A maximum of three I/O extension modules can be attached to a base unit.

Key commercial data

package_quantity	1
GTIN	4046356629522

Technical data

Note:

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	40 mm
Height	103.5 mm
Depth	43 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C

Supply

Supply voltage	24 V DC
Supply voltage range	18 V DC ... 24 V DC
Supply current	100 mA

Analog inputs

Number of inputs	2 (Voltage or current can be chosen separately)
Connection method	Individual wires
Connection method	Screw connection
Input name	Analog inputs
Resolution A/D	12 bit
Limit frequency (3 dB)	5 Hz
Current input signal	0 mA ... 20 mA
Current input signal	4 mA ... 20 mA

I/O extension module - NLC-IO-2AI-2AO-01 - 2701040

Technical data

Analog inputs

Input resistance current input	120 Ω
Voltage input signal	0 V ... 10 V
Voltage input signal	-10 V ... 10 V
Input resistance of voltage input	200 kΩ
Precision	1 %

Analog outputs

Number of outputs	2
Connection method	Individual wires
Connection method	Screw connection
Output name	Analog outputs
D/A resolution	12 bit
Current output signal	0 mA ... 20 mA
Current output signal	4 mA ... 20 mA
Load/output load current output	500 Ω
Voltage output signal	0 V ... 10 V
Load/output load voltage output	1000 Ω
Precision	1 %

classifications

eCl@ss

eCl@ss 4.0	27240101
eCl@ss 4.1	27240101
eCl@ss 5.0	27242216
eCl@ss 5.1	27242216
eCl@ss 6.0	27242216
eCl@ss 7.0	27242216
eCl@ss 8.0	27242216

ETIM

ETIM 2.0	EC001417
ETIM 3.0	EC001417
ETIM 4.0	EC001417
ETIM 5.0	EC001417

UNSPSC


UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

I/O extension module - NLC-IO-2AI-2AO-01 - 2701040

approvals

UL Listed /

Approval details



Drawings

Dimensioned drawing

