

Part Number: SY-Centaur-18G-(length x)M

### Applications:

Connect 4K sources and display for the best image and HDR effect.



# 4K 60H 4:4:4



**ARC**  
Audio return channel

Ethernet



# 18Gbps

**SY Stealth 18G AOC Link**  
High speeds long distance 18Gbps connection via laser beam  
**Centaur 18G AOC**



Max. Resolution 3840x2160  
Support for 4190x2160  
ARC  
RGB to 16Bits colour depth  
REC.2020  
24 to 60Hz refresh rate.  
4:2:0/4:2:2/4:4:4 Colour Sub Sampling.  
1536Hz max audio frequency.  
192/24 max audio resolution.  
Simultaneous dual video stream  
HDR  
Dolby Vision  
HLG

Standard lengths:  
7.5,10,5,20,30m  
Available by special order:  
40,50,60,70,80,90,100m



- 18Gbps
- HDR 1.07 Billion colours
- ARC channel

**Plug and Play, Instant long distance 18Gbps connection.**  
**4K by laser beam.**  
**Slimmer. Faster. Lighter.**

**Best HDR performance.**  
**ARC.**  
**System on chip build with the latest nanotechnology.**

### SPECIFICATIONS

<b>Video resolution</b>	VESA and SMPTE 480p to 2160p with 3D. (All resolutions to: Supports 3840x2160p @24 to 60Hz 4:2:0 to 4:4:4 Colour depth of 8/10/12/16bit. Supports 4096x2160
<b>BANDWIDTH</b>	18Gbps
<b>HDCP</b>	Compatible with all versions up to 2.2v
<b>FEATURES</b>	ARC, Ethernet, Up to 32 audio channels, up to 1536kHz audio sample frequency, up to 192/24 audio resolution. Various other HDMI features included in HDMI 2.0v format. Simultaneous dual video streams, simultaneous audio streams, support for 21:9 aspect ratio, extended CEC protocol, Support HDR, HDR10, Dolby vision, HLG, REC.2020
<b>CONNECTOR</b>	Die cast HDMI type A 19 pins
<b>CONDUCTOR</b>	OM3 Multi-mode optical fibre for Data (3x TMDS + CLK) and Copper lines for DDC Channels (ARC, EDID, HDCP etc)
<b>SLEEVE</b>	PVC
<b>Dimensions and Weights</b>	
<b>Length</b>	7.5/10/15/20/30/40/50/60/70/80/90/100m
<b>OTHER</b>	DDC, CEC, 5V, HEAC, Ethernet, ARC

### Ideal use:

High end 4K home AV systems. An Ideal cable for connection between 4K UHD HD sources and projectors

## The SY Centaur-18G Hybrid AOC

- **4K at the by laser light**  
The fibre optic technology is ready in its current form to exceed HDMI requirements.
- **Guaranteed to support full HDMI 2.0v features**  
3840x2160 (supports 4096x2160), HDR, REC. 2020, 8/10/12/16bit, RGB, YCbCr 4:2:0/4:2:2/4:4:4, 24-60Hz, etc.
- **18Gbps. Nearly twice as fast as HDBaseT**  
Creates the richest images from your Blu-ray with the greatest HDR colours.
- **Metal plugs**  
Preventing emission of RF and interference of WiFi transmission. Ideal solution for multi connector set up such as a rack.
- **Compact. Light. Easy to conceal**  
Nearly 55% lighter than CATx.
- **The latest laser technology**

7.5m, 10m, 15m, 20m, 30m  
additional lengths by special order:  
40,50,60,70,80,90,100m