



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	110	70	60	80	60	280		170	150	150	130			90	30	30	30	40	

Art. no.	11533 060
Cutting edge diameter	6 mm
Werkstückkante	45 Grad
Chamfer angle	90 Degree
Type	N
Number of cutting edges	5 PCS
Surface	ULTRA
Shaft diameter	6 mm
Tool holding device	HB parallel shank
Cutting edge length	1.69 mm
Suitable for material group P	1
Suitable for material group M	1
Suitable for material group K	1
Suitable for material group N	1
Suitable for material group S	2
Suitable for material group H	1

EAN-Code

4050293743418