

Miniature cutting insert, type AP HW56 15

For copy and longitudinal turning

ATORN[®]



Application

For copy and longitudinal turning in the material groups steel and (stainless steel) at low to high cutting speeds and under average cutting conditions.

Version

- Solid carbide cutting insert with 98° working angle with internal cooling

Advantage

- Very hard cemented carbide grade ensures low wear
- Stable geometry, ideal for inside turning
- Extremely sharp blades ensure process reliability for cutting

Art. no.	17120 936
Shaft diameter	10 mm
ISO name	AP
Length	73 mm
Clearance length	35 mm
Radius	0.2 mm
Programming size 2	2 mm
Programming size	4.8 mm
Min. bore diameter	10.1 mm
Machining direction	Left
Carbide type	HW56 15
Material to be processed	Stainless steel, Non-ferrous metal

EAN-Code

4050293374100