

Dot laser, green, 520 nm, 5 mW

DA520-5-3(12x55)-QCW-CON
Order Number: 70133424

Main Parameters (*)	min	typ	max	Unit
Wavelength		520		nm
Optical Output Power		5		mW
Operating Voltage	2.7	3	3.3	V DC
Operating Current	15	50	70	mA
Operating Temperature	-10		60	°C
Storage Temperature	-40		80	°C

Main Data

Warranty	1 years
----------	---------

Technical Parameters

Lifetime	> 6,000 h
RoHS	yes

Optical Parameters

Beam Shape	Dot
Laser Class	3R
Divergence	A - 0.1 mrad
Size of Laserdot	adjustable
Operating Distance	100 m
Optics	glass lens AR coated
Laser technology	Single Mode Diode
Focus	adjustable
internal modulation frequency	1 kHz

Electrical Parameters

Potential of Housing	isolated
Connector	2.5 mm DC plug (GND pole inner)

Mechanical Parameters

Size	Ø12x55 mm
Material	aluminium
Cable length	100 mm
Wire type	26AWG, 0,14mm ²
Output Aperture	5 mm
Housing Color	black
Weight	13 g

(*) Over the complete operating temperature range

Features



- Isolated housing
- Laser Class 3R
- Compact size
- Anti-reflex coating


Picture



Cable color

Ground		black	GND
positive		red	2.7 - 3.3, typ 3 V DC

Safety Label



Valid Revision

| 19-JUL-2019