



Type Designation	2020
Designation IEC	R20 P
System	Carbon Zinc
Shelf Life (Coding)*	36 months
Nominal Voltage [V]	1.5
Typical Capacity C [mAh]	6000 (discharge with high-resistance)
Permissible Temperature Range	- 10 °C ... 50 °C
Weight, approx. [g]	99.2
Volume [ccm]	51.3

Dimensions [mm]	min:	max:
Ø	32.3	34.2
A	-	61.5
B	59.5.6	-
C	18.0	-
E	-	1.0
F	-	9.5
G	1.5	-



**Typical Capacities (at 20°C)**

Discharge Type	Load	End Voltage[V]	0.9
4M/15M, 8H/D, 7D/W	2.2 Ω	Time [m]	380
Portable lighting		Capacity [Ah]	3.42
		Energy [Wh]	3.95
Discharge Type	Load	End Voltage[V]	0.8
1H/D, 7D/W	2.2 Ω	Time [h]	7.85
Toy		Capacity [Ah]	3.75
		Energy [Wh]	4.05
Discharge Type	Load	End Voltage[V]	0.9
4H/D,7D/W	10.0 Ω	Time [h]	42.5
Radio		Capacity [Ah]	5.12
		Energy [Wh]	6.25

**No publication or circulation of data to third parties without consent of VARTA Consumer Batteries**

\* In consideration of typical loss of capacity at storage and application.