

Zero Smog 4V Kit 2 Funnel

Product no.: T0053664699N



Benefits

- › Constant Flow Control (CFC) guarantees automatic air flow regulation for each working place independent of the connected workplaces
- › Electronic filter control with optical and acoustical filter alarm
- › Efficiency test via USB port
- › 4 wheels to allow easy movement of the unit
- › Remote control via RS 232 port
- › Low noise level
- › 4 kits available
- › The fume extraction unit Zero Smog 4V Kit 2 Funnel is easy to install and operate. It is designed for use as a small central system. The kit is supplied complete with 2 pcs. hose connector, flexible hose, flexarm, funnel nozzle, valve and bracket, ready for installation at the workplace. A powerful, maintenance-free turbine provides continuous fume extraction at a maximum air extraction rate of 230 m³/h. With setting constant flow control the adjustable turbine speed avoiding unnecessary waste of suction power and saving energy.



Technical Data

Dimensions L x W x H (mm)	345 x 325 x 505
Dimensions L x W x H (inches)	13,58x12,79x19,88
Weight (approx.) in kg	19
Voltage	220 - 240 V, 50/60 Hz
Power	275 VA
Noise level (distance 1 m) dB(A)	< 48
Max. vacuum	---
Capacity m ³ /h	230
Pre-filter	Pre filter mat class F7
Compact filter	Particle filter H13, Wide band gas filter (50 % Active carbon + 50 % Chemisorb)
Max. capacity	1-4 workstations
RS232 interface (remote control)	All system functions can be operated and remotely monitored via the RS232 port.
USB port	on
WX-compatible	on