Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



1300SB Multi-Conductor - Category 5e ScTP Shipboard ABS Type Approved

Shipboard LAN/Data, WI-FI, Wireless LAN, Outdoor Antenna, Radio, Broadband, RF, Where ABS Type





For more Information please call

1-800-Belden1



General Description:

24 AWG solid bare copper conductors, polypropylene insulation, overall Beldfoil® shield, 24 AWG stranded tinned copper drain wire, low smoke zero halogen jacket.

Approval is Required

8

Suitable Applications:

Physical Characteristics (Overall)

Conductor

Usage (Overall)

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	Solid	BC - Bare Copper

Total Number of Conductors:

Insulation

Insulation Material:

	Wall Thickness (in.)	Dia. (in.)
PP - Polypropylene	.010	.042

Outer Shield

Outer Shield Material:


Outer Shield Trade Name	Туре	Outer Shield Material	Coverage (%)
Beldfoil®	Таре	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

	AWG	Stranding	Drain Wire Conductor Material
ı	24	7x32	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:



Overall Cable

Overall Nominal Diameter: 0.260 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +105°C
Bulk Cable Weight:	32.400 lbs/1000 ft.
Max. Recommended Pulling Tension:	25 lbs.
Min. Bend Radius/Minor Axis:	2.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG-LS
CEC/C(UL) Specification:	CMG-LS
EU Directive 2011/65/EU (ROHS II):	Yes
IEEE Specification:	Std. 45 clause 23

Page 1 of 3 08-26-2016

Detailed Specifications & Technical Data





1300SB Multi-Conductor - Category 5e ScTP Shipboard ABS Type Approved

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	08/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	NEMA WC-63.1 Category 5e, UL 444, ABS Type Approval Certificate 15-VC1420029
Flame Test	
UL Flame Test:	UL1685 FT4 Loading, Limited Smoke
C(UL) Flame Test:	FT4, Limited Smoke
IEC Flame Test:	60332-1, 60332-3-22 (Category A)
IEEE Flame Test:	1202
Suitability	
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes
Plenum/Non-Plenum	
Plenum (Y/N):	No

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)
15

Maximum Capacitance Unbalance (pF/100 m): 330

Nominal Velocity of Propagation:

VP (%) 70

Maximum Delay:

Delay (ns/100 m) 538 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m) 45

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m) 9.38

Max. Operating Voltage - UL:

Voltage 300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)	Min. SRL (dB)
1	2.0	65.3	62.3	60.3	60.3	20.0	20.0
4	4.1	56.3	53.3	49.2	49.2	23.0	23.0
8	5.8	51.8	48.8	43.0	43.0	24.5	24.5
10	6.5	50.3	47.3	40.8	40.8	25.0	25.0
16	8.2	47.3	44.3	36.1	36.1	25.0	25.0
20	9.3	45.8	42.8	33.5	33.5	25.0	25.0
25	10.4	44.3	41.3	30.9	30.9	24.3	24.3
31.25	11.7	42.9	39.9	28.2	28.2	23.6	23.6
62.5	17.0	38.4	35.4	18.4	18.4	21.5	21.5
100	22.0	35.3	32.3	10.3	10.3	20.1	20.1

Page 2 of 3 08-26-2016

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



1300SB Multi-Conductor - Category 5e ScTP Shipboard ABS Type Approved

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	100 ± 15	63.8	60.8
4	100 ± 15	100 ± 15	51.7	48.7
8	100 ± 15	100 ± 15	45.7	42.7
10	100 ± 15	100 ± 15	43.8	40.8
16	100 ± 15	100 ± 15	39.7	36.7
20	100 ± 15	100 ± 15	37.7	34.7
25	100 ± 15	100 ± 15	35.8	32.8
31.25	100 ± 15	100 ± 15	33.9	30.9
62.5	100 ± 15	100 ± 15	27.8	24.8
100	100 ± 15	100 ± 15	23.8	20.8

Notes (Overall)

Notes: RJ-45 Compatible. Jacket sequentially marked at 2 ft. intervals.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1300SB 0101000	1,000 FT	35.000 LB	BLACK	С	4 PR #24 PP FS FRNHPO

Notes: C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 07-15-2016

© 2016 Belden, Inc All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sales believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its bublication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).