

NEOZED-FUSE LINK 400V GL/GG,GR.D02, 40A,
COLLAPSIBLE BOX





Figure similar

Model		
product brand name		SENTRON
Product variations		Pack of 10
Design of the fuse link		NEOZED fuse links
General technical data		
Size of fuse system / acc. to DIN EN 60269-1		D02
Operating class of the fuse link		gG
circuit-breaker / Design		5SE2
Protection class		
Protection class IP		IP20, with connected conductors
Switching capacity		
Switching capacity current / acc. to IEC 60947-2 / Rated value	kA	50
Dissipation		
Active power loss • for rated value of the current / with AC / in hot operating state / per pole	W	3.1
Electricity		
rated current I _n / IEC, DIN/VDE / at 40 Cel	A	38
Current / with AC / Rated value	A	40
Appearance		
Color coding of the fuse link		black
Mechanical Design		

mounting position	Any, preferably vertical
-------------------	--------------------------


Environmental conditions

Ambient temperature	
• minimum	°C -5
• maximum	°C 40

General Product Approval	Test Certificates	other
 	Special Test Certificate Type Test Certificates/Test Report	other Environmental Confirmations

Further information

- Information- and Downloadcenter (Catalogs, Brochures,...)**
<http://www.siemens.com/lowvoltage/catalogs>
- Industry Mall (Online ordering system)**
<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5SE2340>
- Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**
<http://support.automation.siemens.com/WW/view/en/5SE2340/all>
- Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SE2340
- CAx-Online-Generator**
<http://www.siemens.com/cax>
- Tender specifications**
<http://ausschreibungstexte.siemens.com/tiplv>



last modified: 11.03.2015