

Product type designation



RF320T transponder

SIMATIC RF300 TRANSPONDER RF320T BUTTON, 20 BYTE EEPROM, IP 67, -25 TO +125 DEGR/C, D=27 MM X 4 MM MIN. ORDER QUANTITY 20 PCS

Wireless frequencies

Operating frequency / Rated value	13.56 MHz
-----------------------------------	-----------

Electrical data

Range / maximum	60 mm; range is reader dependent: observe http://support.automation.siemens.com/WW/view/en/67384964
Protocol / with radio transmission	RF300-specific
Transfer rate / with radio transmission / maximum	106 kbit/s
Product property / multitag-capable	Yes
Product component / Backup battery	No

Memory

Type of memory	EEPROM
Storage capacity / of the user memory	20 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 20 bytes,
Number of read cycles / at ambient temperature < 40 °C / maximum	100000000000000
Number of write cycles / at ambient temperature < 40 °C / maximum	100000
Data retention time / at ambient temperature < 40 °C / not less than	10 y
Property of memory	Block-by-block write protection of the user memory

Mechanical data

Material	Epoxy resin
Color	black

Mounting distance / relating to metal surfaces / recommended / minimum	20 mm
--	-------

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> during read/write access 	-25 ... +125 °C
<ul style="list-style-type: none"> outside the read/write area 	-40 ... +150 °C
<ul style="list-style-type: none"> during storage 	-40 ... +150 °C
Protection class IP	IP67 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1000 m/s ²
Resistance against vibration	200 m/s ²

Design, dimensions and weight

Height	4 mm
Diameter	27 mm
Net weight	5 g
Mounting type	M3 screw, gluing

Product properties, functions, components / general

Product property	
<ul style="list-style-type: none"> silicon-free 	Yes
<ul style="list-style-type: none"> printable 	No

Standards, specifications, approvals

MTBF	1800 y
------	--------

Accessories

accessories	Mounting support and spacer
-------------	-----------------------------

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> to website: Selector SIMATIC NET SELECTION TOOL 	http://www.siemens.com/snst
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> to website: Information and Download Center 	http://www.siemens.com/automation/net/catalog
<ul style="list-style-type: none"> to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> to website: CAx Download Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> to website: Industry Online Support 	https://support.industry.siemens.com

last modified: 09.03.2015