



Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Range compatibility	P
Flow rate	Free flow rate 44910.05 Gal/hr(US) (170 m3/h) 50 Hz
Input voltage	230 V 50/60 Hz

Complementary

Absorbed power	17 W
Noise level < at	41 dB
Height	External 4.69 in (119 mm)
Width	External 4.69 in (119 mm)
Depth	38 mm external:
Net weight	1.81 lb(US) (0.82 kg)
Material	Protective grille steel
Device composition	1 axial motor 2 protective grille on the front and rear surfaces 1 fixing collar

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	03606480151422
Nbr. of units in pkg.	1
Package weight(Lbs)	1.9 lb(US) (0.86 kg)
Returnability	No
Country of origin	FR

Packing Units

Package 1 Height	2.56 in (65.000 mm)
Package 1 width	5.91 in (150.000 mm)
Package 1 Length	6.50 in (165.000 mm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------
