

Screw tap, HSSE M ISO 2 (6H) 0° 371 B

For use in high-strength steel up to 1300 N/mm²

ATORN[®]



Application

For producing metric threads on CNC machines or conventional machines in **through holes** in the high-strength steel material group up to a strength of 1300 N/mm².

Version

- Dimensions to: DIN 371 = reinforced shank (to M10), DIN 376 = protruding shank (from M12)

Advantage

- Long service life and process reliability through innovative cutting geometry for use in high-strength steel

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	16	12	9																

Art. No.	13130 050
Type	P MAX 1300
Thread type	Metric thread
Thread type x nominal diameter	M5
Pitch	0.8 mm
Hole type	Clearance hole ≤ 3xD
Cutting material	HSSE
Surface	Vaporised
Lead angle shape	B
Tolerance of screw taps	ISO 2 (6H)
Twist angle	0°
Shaft diameter	6 mm
Application type/machine type	CNC, Conventional
Core hole diameter	4.2 mm
Coolant supply	External
Length	70 mm
Shank square	4.9 mm
Cutting speed (steel 1000) suitability	2
Cutting speed (steel 1300) suitability	1
Overall stainless steel suitability	3
fitness not iron total	3
fitness Titan/Nickel/Super total	3
Cutting speed (cast) suitability	3
Cutting speed (hard 55) suitability	3
Cutting speed (hard 65) suitability	3
DIN	371

EAN-Code

4050293017861