



Finish : Reflector

A ( 1 : 1 )

1	0833	2	0833	3	0000	4	<i>m</i> :	5		6		7		8	
SUPERSEDES 9238 529 57900 New Of 14/10/2014				HALOGEN LAMP INFRARED INDUSTRIAL 13245X/98 REFL 380-420V 2000W X					9238 529 57900 0833/000			16/02/2016			
REF. : PDM IRK 2010-069		DOCUMENTATION		UNIT mm	PROJ. EUROP 	2 SH		SH	190-1	10	1:2	A4			
NAME : PI120		VALIDATION : SN928			DR. FISCHER Europe										
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.															

**PRODUCT REQUIREMENT SHEET**

See LV 75-032

<b>MEASURING VOLTAGE</b>	400V (stabilisation 3 min.)
<b>MEASURING POSITION</b>	Horizontal
<b>LIFE TEST POSITION</b>	Horizontal
<b>BURNING POSITION</b>	P15
<b>SWITCHING CYCLE</b>	Continuous
<b>AGEING</b>	1h at rated voltage

	VALUE UNIT	TOLERANCE
<b>WATTAGE</b>	2000W	± 6 %
<b>LIFE</b>	5000 h	average
<b>COLOR TEMPERATURE</b> Clear lamp Lamp with reflector	2450 K 2350 K	± 100 K Indicative value
<b>FLUX (HeLeN lamp)</b>	NA	
<b>WEIGHT</b>	60 g	

1	0833	2	0833	3	0000	4		5		6		7		8	
SUPERSEDES :		HALOGEN LAMP						9238 529 57900			01/12/2010				
9238 529 57900		INFRARED INDUSTRIAL						0833/000							
0833/000 p. 190-2		13245X/98 2000W 400V REFL													
Of 19/08/2002		DOCUMENTATION		UNIT	PROJ EUROP	2	SH	SH	190-2	10			A4		
REF. : IRK N 2009-066				mm											
NOM : PI120		VALIDATION : SN928				DR. FISCHER Europe									
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.															