

TLS Preset Clean Room Torque Screwdrivers

Torque range from 0.04 to 13.6 N.m

Clean Room (CRS) Class 100

Want to know how to use this tool?



Watch our video

Industry Sectors

Manufacturing



Automotive



Electronics



Military



Consumer Products

Slipping Mechanism

Incorrect tightening is impossible



CRS 100-0022 FH



Key Benefits

- These tools are designed to protect precision products from contamination during assembly. They are designed specifically for use in **Clean Rooms** by utilising suitable surface treatments and incorporating high performance seals in their design
- Operator fatigue is minimised by the soft reset action of the tool
- Complete control of the tightening process is achieved by eliminating both under and over tightening as these tools incorporate Torqueleader's slipping mechanism
- Suitable for use by operators of any skill level, as these tools will repeatedly deliver the set torque without the need for operator intervention due to the tamper-proof design

Order now... call our Sales Hotline +44 (0) 1483 894 476

Order Code	Model	Range		Drive	k mm	g	Repeatability	ISO 6789 Class	Colour
		ISO	Imperial						
015089	CRS 100-0022 FH	4-22 cN.m	6-32 ozf-in		104	072	+/- 6%	2F	Grey
015209	CRS 100-0135 FH	10-135 cN.m	0.9-12 lbf-in		111	210	+/- 6%	2F	Grey
015609	CRS 100-0406 FH	50-400 cN.m	4.4-36 lbf-in		127	280	+/- 6%	2F	Grey
015939	CRS 100-1360 FH	2.5-13.6 N.m	22-120 lbf-in		137	325	+/- 6%	2F	Grey



CRS Torque Screwdrivers are preset type torque tools. They must be set to the required value by using a **Torque Analyser**... see pages 45-52 for details