

# Features

# Regulated Converters

- 30mW max. No Load Power Consumption
- High Efficiency up to 80%
- Isolated Output 3kVAC / 1 min
- SCP, OVP Protection
- Wide Operating Temperature Range: -40°C to +85°C
- Universal Input 85-305VAC



## RAC03-SE/277

### 3 Watt Single Output



### Description


The ultra-compact RAC03-SE/277 modules are available with output voltages of 3.3, 5, 12 and 24V, and the input-to-output isolation is 3kVAC/1min. With a standby consumption of 30mW maximum, the mini power supplies are particularly suitable for energy-saving sleep mode and standby applications. Because of its compact design (height <18mm), it is a versatile solution for home automation and other similar applications. Complete with an integrated input filter, the series has enhanced EMI performance and complies with EN55022, class B. The mini power supplies are also protected against short circuit with fully automatic restart after the error has been solved. The converters are EN/UL60950-1 certified and come complete with a 3 year warranty.

### Selection Guide

Part Number	Input Voltage Range (VAC)	Output Voltage (VDC)	Output Current (mA)	Efficiency typ. (%)	Max. Capacitive Load (µF) (1)
RAC03-3.3SE/277	85-305	3.3	900	71	22000
RAC03-05SE/277	85-305	5	600	76	7500
RAC03-12SE/277	85-305	12	250	78	1000
RAC03-24SE/277	85-305	24	125	80	200

**Notes:**

Note1: Test by minimum input and constant resistor load.



### Specifications (measured at TA= 25°C, nominal input voltage (115/230VAC), full load and after warm-up)

BASIC CHARACTERISTICS				
Parameter	Condition	Min.	Typ.	Max.
Input Voltage Range		85VAC 120VDC		305VAC 430VDC
Input Current	full load, 115VAC full load, 230VAC		70mA 45mA	
Inrush Current	cold start at 25°C, 115VAC cold start at 25°C, 230VAC			15A 30A
No load Power Consumption	85-305VAC, 47-440Hz			30mW
Input Frequency Range	AC Input	47Hz		440Hz
Hold-up time	115VAC 230VAC		15ms 80ms	
Operating Frequency Range	100% load at nominal Vin		55kHz	
Efficiency				see Selection Guide
Minimum Load			2%	
Output Ripple and Noise (2)			200mVp-p	

**Notes:**

Note2: Ripple and Noise is the maximum peak-to-peak voltage value measured at the output with a 20MHz bandwidth, at rated line voltage at full load. And with a 47µF low-ESR electrolytic capacitor in parallel with a 0.1µF ceramic capacitor across output.


continued on next page



EN-50155 Certified  
EN-55024 Certified  
EN-60950-1 Certified  
UL-60950-1 Certified

**Specifications** (measured at  $T_A=25^\circ\text{C}$ , nominal input voltage (115/230VAC), full load and after warm-up)

### Efficiency vs. Load



### REGULATIONS

Parameter	Condition	Value
Output Voltage Tolerance <sup>(3)</sup>		±6% max.
Line Voltage Regulation	low line to high line, full load	±1% typ. / ±1.5% max.
Load Voltage Regulation	10% to 100% load	±6% typ.

**Notes:**

Note3: Includes initial voltage accuracy, thermal drift, line regulation and load regulation at rated input voltage and load conditions.


### PROTECTIONS

Parameter	Type	Value
Short Circuit Protection (SCP)		continuous, automatic recovery
Over Voltage Protection (OVP)	Zener Diode clamp	112% - 140%
Over Current Limit		120% - 190%
Isolation Voltage		3kVAC / 1 Minute
Isolation Resistance		1GΩ min.
Leakage Current	85-305VAC, 47-440kHz	10μA max.

**Notes:**

Note4: An input fuse must be always used. Recommended fuse: T1A slow blow type

Note5: An external MOV is required. The Varistor should comply with IEC-61051-2. e.g. EPCOS S14 Series



**Specifications** (measured at  $T_A=25^\circ\text{C}$ , nominal input voltage (115/230VAC), full load and after warm-up)


ENVIRONMENTAL		
Parameter	Condition	Value
Operating Temperature Range	with derating (see graph)	-40°C to +85°C
Maximum Case Temperature		105°C
Thermal Impedance		10°C / W typ.
Humidity	non-condensing	5% - 95%, RH max.
MTBF <sup>(6)</sup>	MIL-HDBK-217F, 115VAC, +25°C MIL-HDBK-217F, 230VAC, +25°C	3503 x 10 <sup>3</sup> hours 1816 x 10 <sup>3</sup> hours

**Notes:**


Note6: MTBF is referring RAC03-3.3SE/277

**Derating Graph**

**@ 85-140VAC**



**@ 140-305VAC**



**SAFETY AND CERTIFICATIONS**

Certificate Type	Report / File Number	Standard
EN General Safety	SPCLVD1208051	EN-60950-1, 2nd Edition
UL General Safety	E224736-X1-A24	UL-60950-1, 2nd Edition, 2014
Canada General Safety	E224736-X1-A24	CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014






Certificate Type (Environmental)	Report / File Number	Standard / Criterion
ESD	±8kV Air Discharge; ±6kV Contact	EN61000-4-2, Criteria B
Radiated Immunity	3V/m	EN61000-4-3, Criteria A
Fast Transient	AC Power Port: ±1kV	EN61000-4-4, Criteria B
Surge	AC Power Port: line to line: ±1kV	EN61000-4-5, Criteria B
Conducted Immunity	AC Power Port: 3V/m	EN61000-4-6, Criteria A
Power Magnetic Field	1 A/m	EN61000-4-8, Criteria A
Voltage Dips and Interruption	Voltage Dips: >95% reduction >30% reduction	EN61000-4-11, Criteria B EN61000-4-11, Criteria C
Voltage flicker	Interruption: >95%	EN61000-4-11, Criteria C EN61000-3-3
EMI Standard	Report: 1502CE17	EN55022, Class B EN55024
Vibration		MIL-STD-202G
Over Voltage Category		OVC II

**Specifications** (measured at  $T_A = 25^\circ\text{C}$ , nominal input voltage (115/230VAC), full load and after warm-up)

### DIMENSION and PHYSICAL CHARACTERISTICS

Parameter	Type	Value
Case Material		UL94V-0, black plastic
Potting Material		UL94V-0, Silicone
Package Dimension (LxWxH)		38.25 x 24.35 x 17.4mm
Package Weight		28g typ.

#### Dimension Drawing (mm)



#### Pin Connections

Pin #	Single
1	VAC in (L)
3	VAC in (N)
13	NC
14	-Vout
16	+Vout

NC no connection

Tolerance: xx.x= ±0.5mm

xx.xx= ±0.35mm

Pin width: ±0.05mm

### PACKAGING INFORMATION

Parameter	Type	Value
Packaging Dimension (LxWxH)	Tube	520 x 32 x 27mm
Packaging Quantity		12 pcs.
Storage Temperature Range		-40°C to +85°C