



**RCD/RCB, 10A, 100mA, miniature circuit-breaker trip curve B, 2 p,
residual current circuit-breaker trip characteristic: A**

Part no. PKPM2-10/2/B/01-A
Article no. 108113

Similar to illustration

Delivery programme

Basic function			Combined RCD/RCB devices
Number of poles			2 pole
Tripping characteristic			B
Application			Switchgear for residential and commercial applications
Rated current	I_n	A	10
Rated switching capacity according to IEC/EN 61009		kA	10
Rated fault current	$I_{\Delta N}$	A	0.1
Type			Type A
Tripping		A	non-delayed
Product range			PKPM2
Sensitivity			Pulse-current sensitive
Impulse withstand current			Partly surge-proof 250 A

Technical data

Electrical

Sensitivity			Pulse-current sensitive
-------------	--	--	-------------------------

Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	I_n	A	10
Heat dissipation per pole, current-dependent	P_{vid}	W	0
Equipment heat dissipation, current-dependent	P_{vid}	W	4.3
Static heat dissipation, non-current-dependent	P_{vs}	W	0
Heat dissipation capacity	P_{diss}	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	40
			0
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			
			Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures			
			Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat			
			Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects			
			Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation			
			Meets the product standard's requirements.
10.2.5 Lifting			
			Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact			
			Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions			
			Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES			
			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			
			Meets the product standard's requirements.
10.5 Protection against electric shock			
			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			
			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			
			Is the panel builder's responsibility.
10.8 Connections for external conductors			
			Is the panel builder's responsibility.
10.9 Insulation properties			

10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 6.0

Circuit breakers and fuses (EG000020) / Earth leakage circuit breaker (EC000905)		
Electric engineering, automation, process control engineering / Electrical installation, device / Residual current protection system / MCB/RCCB combination (ecl@ss8.1-27-14-22-07 [AFZ810012])		
Number of poles (total)		2
Number of protected poles		2
Nominal rated voltage	V	230
Nominal rated current	A	10
Rated fault current	A	0.1
Leakage current type		A
Current limiting class		3
Rated short-circuit breaking capacity EN 60898	kA	10
Rated short-circuit breaking capacity IEC 60947-2	kA	0
Frequency		50 Hz
Release characteristic		B
Concurrently switching N-neutral		No
Over voltage category		3
Pollution degree		2
Width in number of modular spacings		2
Built-in depth	mm	70
Suitable for flush-mounted installation		No
Degree of protection (IP)		IP20
Surge current capacity	kA	0.25
Voltage type		AC
Antinuisance tripping version		No