



### Model Number

NMB3-8GM35-E2

### Features

- 3 mm flush
- Stainless steel sensing face
- Increased operating distance

## Technical Data

### General specifications

Switching element function		PNP	NO
Rated operating distance	$s_n$	3 mm	
Installation		flush	
Output polarity		DC	
Assured operating distance	$s_a$	0 ... 2.43 mm	
Reduction factor $r_{Al}$		0.3	
Reduction factor $r_{Cu}$		0.2	
Reduction factor $r_{304}$		0.7	

### Nominal ratings

Operating voltage	$U_B$	10 ... 30 V DC
Switching frequency	$f$	0 ... 360 Hz
Hysteresis	$H$	5 ... 15 typ. 10 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	$U_d$	$\leq 2$ V
Operating current	$I_L$	0 ... 100 mA
Off-state current	$I_r$	0 ... 10 $\mu$ A typ. 0.1 $\mu$ A at 25 °C
No-load supply current	$I_0$	$\leq 10$ mA
Switching state indicator		LED, red

### Functional safety related parameters

MTTF <sub>d</sub>	2000 a
Mission Time ( $T_M$ )	20 a
Diagnostic Coverage (DC)	0 %

### Standard conformity

Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007
-----------	---

### Ambient conditions

Ambient temperature	-25 ... 75 °C (-13 ... 167 °F)
---------------------	--------------------------------


### Mechanical specifications

Connection type	cable PUR, 2 m
Core cross-section	0.14 mm <sup>2</sup>
Housing material	Stainless steel 1.4305 / AISI 303
Sensing face	Stainless steel 1.4305 / AISI 303
Degree of protection	IP67

### Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	CCC approval / marking not required for products rated $\leq 36$ V

## Dimensions



## Electrical Connection

