

Miniature cutting insert, type AQ HC56 15

For copy and longitudinal turning

ATORN[®]

Application

For copy and longitudinal turning in the material groups steel, stainless steel and special alloys, hard machining up to 65 HRC at high cutting speeds and under average cutting conditions.

Version

- Solid carbide cutting insert with 98° working angle with internal cooling

Advantage

- Very hard cemented carbide grade ensures low wear
- Stable geometry, ideal for inside turning
- Innovative coating technology for universal use with very high service life requirements



Art. no.	17121 180
Shaft diameter	4 mm
ISO name	AP
Length	51 mm
Clearance length	10 mm
Radius	0.2 mm
Programming size 2	0.8 mm
Programming size	1.8 mm
Min. bore diameter	4.1 mm
Machining direction	Right
Carbide type	HC56 15
Material to be processed	Steel, Stainless steel, Special alloy, Hardened material

EAN-Code

4050293374384