

SITOR-FUSE-LINK FOR SEMICONDUCTOR
 PROTECTION 1100A AR 800V A.C. MBC=6XIN SIZE 3
 WITH FLUSH-END CONTACTS M12

Model		
product brand name		SETRON
Design of an identification indicator		others
Design of the fuse link		SITOR, LV HRC design

General technical data		
Size of fuse system / acc. to DIN EN 60269-1		NH3
Operating class of the fuse link		aR
circuit-breaker / Design		3NC

Switching capacity		
Switching capacity current		
<ul style="list-style-type: none"> acc. to IEC 60947-2 / Rated value 	kA	100

Dissipation		
Active power loss		
<ul style="list-style-type: none"> for rated value of the current / with AC / in hot operating state / per pole 	W	175

Electricity		
rated current I _n / IEC, DIN/VDE / at 40 Cel	A	1 045
Current / with AC / Rated value	A	1 100

Mechanical Design		
mounting position		Any, preferably vertical

Environmental conditions		
Ambient temperature		
<ul style="list-style-type: none"> minimum 	°C	-20
<ul style="list-style-type: none"> maximum 	°C	50

Certificates		
Equipment marking		
<ul style="list-style-type: none"> acc. to DIN EN 61346-2 		F
<ul style="list-style-type: none"> acc. to DIN EN 81346-2 		F



CCC



GOST



UL



EG-Konf.

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)<http://www.siemens.com/lowvoltage/catalogs>**Industry Mall (Online ordering system)**<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NC33426U>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<http://support.automation.siemens.com/WW/view/en/3NC33426U/all>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NC33426U**CAX-Online-Generator**<http://www.siemens.com/cax>**Tender specifications**<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015