

Abisolier-Seitenschneider Professional electric mit DynamicJoint®




Z 14 0 06

Best.-Nr.	mm	II	✂	Ømm	SB	📦
26745	160	6 1/2"	13	1.6		5
27431	160	6 1/2"	13	1.6	x	5

DIN ISO 5749. Geprüft gemäß IEC 60900.

Seitenschneider Professional electric mit DynamicJoint®



Z 12 1 06

Best.-Nr.	mm	II	✂	Ømm	SB	📦
43326	140	5 1/2"	16	1,6		5
43453	140	5 1/2"	16	1,6	x	5
43335	160	6 1/2"	17	2		5
43458	160	6 1/2"	17	2	x	5
43340	180	7"	18	2,3		5
43463	180	7"	18	2,8	x	5

Geprüft gemäß IEC 60900.

Hochleistungs-Seitenschneider BiCut® Professional electric mit DynamicJoint®



 red dot award 2014 winner

Z 18 0 06

umschaltbar

Best.-Nr.	mm	II	✂	Ømm	SB	📦
38191	200	8	21	3		5
38984	200	8	21	3	x	5

Geprüft gemäß IEC 60900.

Seitenschneider Industrial electric mit DynamicJoint®



Z 12 1 09

Best.-Nr.	mm	II	✂	Ømm	SB	📦
43327	140	5 1/2"	16	1,6		5
43454	140	5 1/2"	16	1,6	x	5
43336	160	6 1/2"	17	2		5
43459	160	6 1/2"	17	2	x	5
43341	180	6"	18	2,8		5
43464	180	7"	18	2,8	x	5

Geprüft gemäß IEC 60900.