

ACT26JD19HE [V001] ✓ ACTIVE

DEUTSCH | DEUTSCH 38999 Series III Composite Connectors

TE Internal #: YACT26JD19HEV00100

Standard Circular Connectors, Cable-to-Panel, 19 Position,
Sealable, Wire & Cable, Signal, Panel Mount, DEUTSCH 38999
Series III Composite Connectors

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors > Straight Plug D38999, D19 Insert



Connector System: **Cable-to-Panel**

Number of Positions: **19**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **7.5 A**

[All Straight Plug D38999, D19 Insert \(75\)](#)

Features

Product Type Features

| | |
|-----------------------------------|----------------------|
| Product Type | Connector |
| Assembly Type | Electrical Connector |
| Connector System | Cable-to-Panel |
| Sealable | Yes |
| Connector & Contact Terminates To | Wire & Cable |
| Circular Connector Type | Plug |
| Shell Type | Straight Plug |

Configuration Features

| | |
|---------------------------------------|--------------------|
| Keying & Polarized Position Locations | E |
| Factory Installed Backshell | No |
| Keying | Key Polarization E |
| Number of Positions | 19 |
| Number of Power Positions | 0 |
| Number of Signal Positions | 19 |
| Contacts Preloaded | No |

Electrical Characteristics



| | |
|-------------------|---------|
| Operating Voltage | 600 VAC |
|-------------------|---------|

| | |
|---------|-----------|
| Voltage | 1800 Vrms |
|---------|-----------|

Body Features

| | |
|--------------------------|-----|
| Environmental Protection | Yes |
|--------------------------|-----|

| | |
|--------|------------------|
| Weight | 18.3 g[.0404 lb] |
|--------|------------------|

| | |
|------------------|----|
| Feedthrough Type | No |
|------------------|----|

| | |
|-------------------------------|------------------|
| Environmental Protection Type | Elastomer Sealed |
|-------------------------------|------------------|

| | |
|-------------|----------------|
| Entry Style | Rear Insertion |
|-------------|----------------|

| | |
|------------|--|
| Fluid Type | Coolanol 25, M2-V, MIL-DTL-5624 (JP-4,JP-5), MIL-DTL-83133 (JP-8), MIL-PRF-23699, MIL-PRF-5606, MIL-PRF-7808, SEA-AMS1424 Type I |
|------------|--|

| | |
|------------------------|---------------|
| Shell Plating Material | Cadmium, O.D. |
|------------------------|---------------|

| | |
|---------------------|-----------|
| Shell Base Material | Composite |
|---------------------|-----------|

| | |
|---|--------------------------|
| Circular Connector Insulation Material Type | Hard Dielectric/Silicone |
|---|--------------------------|

| | |
|---------------------|----|
| Hermetically Sealed | No |
|---------------------|----|

Contact Features

| | |
|----------------------------|----|
| Contact Quantity (Size 20) | 19 |
|----------------------------|----|

| | |
|------------------------------|-------|
| Contact Current Rating (Max) | 7.5 A |
|------------------------------|-------|

| | |
|----------------|----|
| Reverse Gender | No |
|----------------|----|

| | |
|----------------------------|-----|
| Contact Layout Arrangement | D19 |
|----------------------------|-----|

| | |
|---------------------------------|-----|
| Circular Connector Contact Type | Pin |
|---------------------------------|-----|

Mechanical Attachment

| | |
|-----------------------|-----------------------|
| Mating Retention Type | Triple Start Threaded |
|-----------------------|-----------------------|

| | |
|---------------------|---------|
| Panel Mount Feature | Without |
|---------------------|---------|

| | |
|-------------------------|-------------|
| Connector Mounting Type | Panel Mount |
|-------------------------|-------------|

| | |
|-------------------|---|
| Polarization Code | E |
|-------------------|---|

| | |
|-----------------------|-------|
| Mating Alignment Type | Keyed |
|-----------------------|-------|

| | |
|------------------|------|
| Mating Retention | With |
|------------------|------|

Housing Features

| | |
|-------------------------------|----|
| Circular Connector Shell Size | 15 |
|-------------------------------|----|

| | |
|-----------------|----------|
| Alignment Keyed | Clocking |
|-----------------|----------|

Dimensions

| | |
|--|--|
| | |
|--|--|



| | |
|--|--------------------------------|
| Accepts Wire Insulation Diameter Range | 1.02 – 2.11 mm [.04 – .083 in] |
| Assembly Length | 31.5 mm [1.24 in] |
| Wire Size | .2 – .52 mm ² |

Usage Conditions

| | |
|-----------------------------|-----------------------------|
| Fluid Resistance | Yes |
| Operating Temperature Range | -65 – 200 °C [-85 – 392 °F] |

Operation/Application

| | |
|---------------------|-------------|
| Durability Rating | 1500 Cycles |
| Circuit Application | Signal |
| Shielded | Yes |

Packaging Features

| | |
|--------------------|---|
| Packaging Quantity | 1 |
|--------------------|---|

Other

| | |
|----------------------------|-----|
| Position Locations Omitted | All |
|----------------------------|-----|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Not Compliant |
| EU ELV Directive 2000/53/EC | Not Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Cd (3.45% in Plating) Pb (1.2% in Contact Lead-Coper Alloy) Decamethylcyclopentasiloxane (D5) (5% in Insert Subassembly) <small>Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small> |
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as

EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Also in the Series | DEUTSCH 38999 Series III Composite Connectors



Customers Also Bought





Documents

Product Drawings

[STRAIGHT PLUG](#)

English

Datasheets & Catalog Pages

[DEUTSCH MIL-DTL-38999 Connectors Quick Reference Guide](#)

English