

Data Sheet

ADATA NH13 portable HDD

External Storage Devices

Ultimate Portability, Anytime and Anywhere

The ADATA NH13 portable HDD with 2TB and its USB 3.0 interface is three times faster than most USB 2.0 hard drives available in the market. In addition to speed, the NH13 has a fine brushed metal surface with a matching streamlined design, giving it an overall appearance of slimness and elegance. The NH13 is loss from impact shock. Compared to USB 2.0, in file read/write or data backup-, transmission time can be significantly reduced, up to 70%



Elegant and thin design

- The NH13 has a brushed metal exterior in a streamlined shape, for a thin and elegant overall appearance.

SuperSpeed USB 3.0 performance (backward compatible with USB 2.0)

- The NH13 is equipped with a SuperSpeed USB 3.0 transfer interface, nearly three times faster than USB 2.0.

Bright blue LED indicator

- The NH13 features a bright blue LED indicator that shines through the enclosure to indicate power and data transfer status.

One-touch backup

- With one easy touch, all data can be automatically backed up and synchronised.

NH13 portable HDD

Technical specifications

Hard disk capacity	2 TB
Required interface	USB 3.0, USB 2.0
Notes	USB Bus Powered / 500 mA require
LED	Blue to indicate power and data transfer status
Color	Silver

Interfaces

Interfaces	USB 3.0
Required interface	USB 3.0, USB 2.0
System requirements	Free USB port
Supported operating systems	Windows 8.1 Windows 8 Windows 7 MacOS™ 10.8 or later Mac OS X

Device Classification

Power consumption	Suspend Current: < 1W Stand by Current: < 1.75 W Active Current: <4.38 W
-------------------	--

Compliance

Europe	CE
USA/Canada	FCC Class A
Japan	VCCI
Taiwan	BSMI
Compliance link	https://sp.ts.fujitsu.com/sites/certificates

Dimensions / Weight / Environmental

Dimensions (W x D x H)	78 mm (3 in) x 119 mm (4.6 in) x 16 mm (0.6 in)
Weight	0.180 kg (5.8 oz)
Operating ambient temperature	5 - 50 °C
Storage ambient temperature	-40 - 60°C

Package content

	NH13 portable HDD USB3.0 cable Quick Start Guide
--	--

Order information

	S26391-F6048-L420	EAN: 4057185511629	2 TB
--	-------------------	--------------------	------

Warranty

Warranty period	2 years (depending on country)
Warranty type	Bring-In / Send-In Service (depending on country)
Warranty Terms & Conditions	http://support.ts.fujitsu.com/warranty
Service Weblink	http://www.fujitsu.com/fts/services/support

More information

Fujitsu OPTIMIZATION Services

In addition to ADATA NH13 portable HDD, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

Fujitsu Portfolio

Build on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offering. This allows customers to leverage from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

Computing Products

www.fujitsu.com/global/products/computing/

Software

www.fujitsu.com/software/

More information

Learn more about ADATA NH13 portable HDD, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.
www.fujitsu.com/fts/accessories

Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment. Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at <http://www.fujitsu.com/global/about/environment>



Copyrights

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see www.fujitsu.com/terms
© 2017 Fujitsu Technology Solutions GmbH

Disclaimer

Technical data is subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

Contact

Fujitsu Technology Solutions GmbH
Website: www.fujitsu.com/fts
2017-08-18 CE-EN

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see www.fujitsu.com/terms
© 2017 Fujitsu Technology Solutions GmbH