

SIMATIC ET 200SP, TM count 1x 24 V Counter module, 1 channel for 24 V incremental encoder or pulse encoder, 3 DI, 2 DQ Suitable for BU type A0, packing quantity: 1 unit,



General information	
Product type designation	TM Count 1x24V
Firmware version	V2.0
<ul style="list-style-type: none"> FW update possible 	Yes
usable BaseUnits	BU type A0
Color code for module-specific color identification plate	CC00
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M3
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated as of version 	STEP 7 V15 SP1 or higher
<ul style="list-style-type: none"> STEP 7 configurable/integrated as of version 	V5.6 and higher
<ul style="list-style-type: none"> PROFIBUS as of GSD version/GSD revision 	One GSD file each, Revision 3 and 5 and higher
<ul style="list-style-type: none"> PROFINET as of GSD version/GSD revision 	GSDML V2.34
Supply voltage	
Load voltage L+	
<ul style="list-style-type: none"> Rated value (DC) 	24 V

- permissible range, lower limit (DC) 19.2 V
- permissible range, upper limit (DC) 28.8 V
- Reverse polarity protection Yes

Input current

Current consumption, max. 60 mA; without load

Encoder supply

Number of outputs 1

24 V encoder supply

- 24 V Yes; L+ (-0.8 V)
- Short-circuit protection Yes; electronic/thermal
- Output current, max. 300 mA

Power loss

Power loss, typ. 1 W

Address area

Address space per module

- Inputs 16 byte; 4 bytes in Fast mode
- Outputs 12 byte; 4 bytes for Motion Control, 0 bytes for Fast mode

Digital inputs

Number of digital inputs 3

Digital inputs, parameterizable Yes

Input characteristic curve in accordance with IEC 61131, type 3 Yes

Digital input functions, parameterizable

- Gate start/stop Yes
- Capture Yes
- Synchronization Yes
- Freely usable digital input Yes
- Probe Yes

Input voltage

- Rated value (DC) 24 V
- for signal "0" -5 ... +5 V
- for signal "1" +11 to +30V
- permissible voltage at input, min. -30 V; -5 V continuous, -30 V brief reverse polarity protection
- permissible voltage at input, max. 30 V

Input current

- for signal "1", typ. 2.5 mA

Input delay (for rated value of input voltage)

for standard inputs

- parameterizable Yes; none / 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms
- at "0" to "1", min. 6 µs; for parameterization "none"

— at "1" to "0", min.	6 µs; for parameterization "none"
for technological functions	
— parameterizable	Yes
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Digital outputs	
Type of digital output	Transistor
Number of digital outputs	2
Digital outputs, parameterizable	Yes
Short-circuit protection	Yes; electronic/thermal
• Response threshold, typ.	1 A
Limitation of inductive shutdown voltage to	L+ (-53 V)
Controlling a digital input	Yes
Digital output functions, parameterizable	
• Switching tripped by comparison values	Yes
• Freely usable digital output	Yes
Switching capacity of the outputs	
• with resistive load, max.	0.5 A; Per digital output
• on lamp load, max.	5 W
Load resistance range	
• lower limit	48 Ω
• upper limit	12 kΩ
Output voltage	
• for signal "1", min.	23.2 V; L+ (-0.8 V)
Output current	
• for signal "1" rated value	0.5 A; Per digital output
• for signal "1" permissible range, max.	0.6 A; Per digital output
• for signal "1" minimum load current	2 mA
• for signal "0" residual current, max.	0.5 mA
Output delay with resistive load	
• "0" to "1", max.	50 µs
• "1" to "0", max.	50 µs
Switching frequency	
• with resistive load, max.	10 kHz
• with inductive load, max.	0.5 Hz; Acc. to IEC 60947-5-1, DC-13; observe derating curve
• on lamp load, max.	10 Hz
Total current of the outputs	
• Current per module, max.	1 A
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m

Encoder	
Connectable encoders	
<ul style="list-style-type: none"> • 2-wire sensor <ul style="list-style-type: none"> — permissible quiescent current (2-wire sensor), max. 	Yes 1.5 mA
Encoder signals, incremental encoder (asymmetrical)	
<ul style="list-style-type: none"> • Input voltage • Input frequency, max. • Counting frequency, max. • Cable length, shielded, max. • Signal filter, parameterizable • Incremental encoder with A/B tracks, 90° phase offset • Incremental encoder with A/B tracks, 90° phase offset and zero track • Pulse encoder • Pulse encoder with direction • Pulse encoder with one impulse signal per count direction 	24 V 200 kHz 800 kHz; with quadruple evaluation 600 m; depending on input frequency, encoder and cable quality; max. 50 m at 200 kHz Yes Yes Yes Yes Yes Yes Yes
Encoder signal 24 V	
<ul style="list-style-type: none"> — permissible voltage at input, min. — permissible voltage at input, max. 	-30 V; -5 V continuous, -30 V brief reverse polarity protection 30 V
Interface types	
<ul style="list-style-type: none"> • Source/sink input • Input characteristic curve in accordance with IEC 61131, type 3 	Yes Yes
Interrupts/diagnostics/status information	
Substitute values connectable	Yes; Parameterizable
Alarms	
<ul style="list-style-type: none"> • Diagnostic alarm • Hardware interrupt 	Yes Yes
Diagnostic messages	
<ul style="list-style-type: none"> • Monitoring the supply voltage • Wire-break • Short-circuit • A/B transition error at incremental encoder • Group error 	Yes Yes Yes Yes Yes
Diagnostics indication LED	
<ul style="list-style-type: none"> • Monitoring of the supply voltage (PWR-LED) • Channel status display • for module diagnostics 	Yes; green PWR LED Yes; green LED Yes; green/red DIAG LED

- Status indicator forward counting (green)
- Status indicator backward counting (green)

Yes
Yes

Integrated Functions

Number of counters	1
Counting frequency (counter) max.	800 kHz; with quadruple evaluation
Fast mode	Yes

Counting functions

• Can be used with TO High_Speed_Counter	Yes
• Continuous counting	Yes
• Counter response parameterizable	Yes
• Hardware gate via digital input	Yes
• Software gate	Yes
• Event-controlled stop	Yes
• Synchronization via digital input	Yes
• Counting range, parameterizable	Yes

Comparator

— Number of comparators	2
— Direction dependency	Yes
— Can be changed from user program	Yes

Position detection

• Incremental acquisition	Yes
• Suitable for S7-1500 Motion Control	Yes

Measuring functions

• Measuring time, parameterizable	Yes
• Dynamic measurement period adjustment	Yes
• Number of thresholds, parameterizable	2

Measuring range

— Frequency measurement, min.	0.04 Hz
— Frequency measurement, max.	800 kHz
— Cycle duration measurement, min.	1.25 μ s
— Cycle duration measurement, max.	25 s

Accuracy

— Frequency measurement	100 ppm; depending on measuring interval and signal evaluation
— Cycle duration measurement	100 ppm; depending on measuring interval and signal evaluation
— Velocity measurement	100 ppm; depending on measuring interval and signal evaluation

Potential separation

Potential separation channels

• between the channels and backplane bus	Yes
--	-----

Isolation

Isolation tested with	707 V DC (type test)
-----------------------	----------------------

Ambient conditions

Ambient temperature during operation

• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
• ceiling installation, min.	-30 °C
• ceiling installation, max.	50 °C
• floor installation, min.	-30 °C
• floor installation, max.	50 °C

Altitude during operation relating to sea level

• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
---	--

Decentralized operation

to SIMATIC S7-300	Yes
to SIMATIC S7-400	Yes
to SIMATIC S7-1200	Yes
to SIMATIC S7-1500	Yes
to standard PROFIBUS master	Yes
to standard PROFINET controller	Yes

Dimensions

Width	15 mm
Height	73 mm
Depth	58 mm

Weights

Weight, approx.	45 g
-----------------	------

last modified: 03/31/2020