

EKI-2725

EKI-2728

5-port Gigabit Unmanaged Industrial Ethernet Switch

8-port Gigabit Unmanaged Industrial Ethernet Switch

NEW



EKI-2725

EKI-2728



Features

- Provides 5 or 8 Gigabit Ethernet ports with Auto MDI/MDI-X
- Supports 10/100/1000Mbps Auto Negotiation
- Supports jumbo frame transmission up to 9kbytes
- Supports 4,000 V_{DC} Ethernet ESD protection
- Provides surge (EFT) protection 3,000 V_{DC} for power line
- Provides Slim size, DIN-rail with IP30 metal mechanism
- Supports Redundant 12 ~ 48 V_{DC} power input and P-Fail Relay
- Provides broadcast storm protection

Introduction

The EKI-2725/2728 supports Gigabit Ethernet and has a +12 ~ 48 V_{DC} redundant power input design, and is secured with a double protection mechanism; Power Polarity Reverse Protect and an Overload Current Resettable Fuse. The former tolerates reverse power wiring (devices will not be damaged if the plus and minus power cables are mixed, even continuing to operate normally. The later secures the system from overload currents; when the power supply turns normal, EKI-2725/2728 will automatically get back to work. Each port of EKI-2725/2728 has 2 LED's to show the link status transmission speed and collision status. It also provides a relay output for an event alarm. In the event of a power failure, the built-in LED will activate the alarm to notify administrators. Engineers can simply verify the hardware status by checking the LED, and have troubleshooting easy and quick. EKI-2725/2728 comes with compact metal housing that rates IP30 to help against from dusty industrial environments.

Specifications

Communications

- **Standard** IEEE 802.3, 802.3u, 802.3x, 802.3ab
- **LAN** 100Base-TX, 10/1000Base-T
- **Transmission Distance** Up to 100m (4-wire Cat.5e, Cat.6 RJ-45 cable)
- **Transmission Speed** Up to 1000 Mbps

Interface

- **Connectors** 5 x RJ-45 (EKI-2725) or 8 x RJ-45 (EKI-2728)
6-pin removable screw terminal (power & relay)
- **LED Indicators** P1, P2, P-Fail
10/100/1000T(X): Link/Activity, Duplex/Collision

Power

- **Power Consumption** Max. 4.6W
- **Power Input** 12 ~ 48 V_{DC}, redundant dual inputs
- **Fault Output** 1 Relay Output

Mechanism

- **Dimensions (W x H x D)** 37 x 140 x 95 mm
- **Enclosure** IP30, Metal shell with solid mounting kits
- **Mounting** DIN-rail, Wall

Protection

- **ESD (Ethernet)** 4,000 V_{DC}
- **Surge (EFT for power)** 3,000 V_{DC}
- **Power Reverse** Present
- **Overload** EKI-2725: 0.9 A @ 12 V_{DC} (Re-settable Fuse)
EKI-2728: 1.6 A @ 12 V_{DC} (Re-settable Fuse)

Environment

- **Operating Temperature** -10 ~ 60° C (14 ~ 140° F)
- **Storage Temperature** -40 ~ 85° C (-40 ~ 185° F)
- **Operating Humidity** 5 ~ 95% (non-condensing)
- **Storage Humidity** 0 ~ 95% (non-condensing)
- **MTBF** 627,958 hrs

Certifications

- **Safety** UL 60950-1, CAN/CSA-C22.2 No.60950
- **EMC** U.S.A.: FCC Part 15 CISPR 22
EU: EN55011, EN61000-6-4
EN55022 Class A,
EN61000-3-2/3
EN55024
IEC61000-4-2/3/4/5/6/8
EN61000-6-2
- **Shock** IEC60068-2-27
- **Freefall** IEC60068-2-32
- **Vibration** IEC60068-2-6

Ordering Information

- **EKI-2725** 5-port Gigabit Ethernet Switch
- **EKI-2728** 8-port Gigabit Ethernet Switch