


Selection Guide of Clamp Meters

| MODEL | AC Clamp Meters | | | | | | | | | |
|-------------------------|---|---|---|---|---|---|---|---|---|---|
| | 2608A | 2805 | 2006 | 2007A | 2031 | 2017 | 2027 | 2040 | 2002PA | 2002R |
| Appearance |  |  |  |  |  |  |  |  |  |  |
| Display | Analogue | Analogue | Digital | Digital | Digital | Digital | Digital | Digital | Digital | Digital |
| Sample rate | — | — | 2 counts / sec | Approx. 2.5 counts / sec | 2 counts / sec | Approx. 2.5 counts / sec | Approx. 2.5 counts / sec | 3 counts / sec | Approx. 2.5 counts / sec | Approx. 2.5 counts / sec |
| Detection method | MEAN | MEAN | MEAN | MEAN | MEAN | MEAN | RMS | MEAN | MEAN | RMS |
| Frequency response | 50/60Hz | 50/60Hz | 40Hz~1kHz | 40~400Hz | 40Hz~1kHz | 45Hz~1kHz | 40Hz~1kHz | 40~400Hz | 40Hz~1kHz | 40Hz~1kHz |
| Conductor size (MAX.mm) | φ 33mm | φ 35mm | φ 19mm | φ 33mm | φ 24mm | φ 33mm | φ 33mm | φ 33mm | φ 55mm | φ 55mm |
| Measurement | | | | | | | | | | |
| AC A Resolution | 300A 0.2A | 600A 0.2A | 200A 0.001A | 600A 0.1A | 20A 0.01A | 600A 0.1A | 600A 0.1A | 600A 0.1A | 2000A 0.1A | 2000A 0.1A |
| DC A Resolution | — | — | — | — | — | — | — | — | — | — |
| AC V | 600V | 600V | 500V | 750V | — | 600V | 600V | 600V | 750V | 750V |
| DC V | 60V | — | 500V | — | — | — | — | 600V | 1000V | 1000V |
| Resistance | 10kΩ | 2kΩ | 2kΩ | 4000Ω | — | 200Ω | 200Ω | 60MΩ | 400kΩ | 400kΩ |
| Continuity buzzer | — | — | ○ | ○ | — | ○ | ○ | ○ | ○ | ○ |
| Frequency | — | — | — | — | — | — | — | 10kHz | — | — |
| DUTY | — | — | — | — | — | — | — | ○ | — | — |
| Dioded test | — | — | — | — | — | — | — | ○ | — | — |
| Capacitance test | — | — | — | — | — | — | — | — | — | — |
| Temperature | -20~150°C | — | — | — | — | — | — | — | — | — |
| Function | | | | | | | | | | |
| NCV | — | — | — | — | — | — | — | ○ | — | — |
| Back light | — | — | — | — | — | — | — | — | — | — |
| Data hold | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| Peak hold | — | — | — | — | — | — | — | ○ | ○ | ○ |
| MAX/MIN | — | — | — | — | — | — | — | ○ | — | — |
| REL | — | — | — | — | — | — | — | ○ | — | — |
| Analogue output | — | — | — | — | — | — | — | — | ○(DC400mV) | ○(DC400mV) |
| Frequency filter | — | — | — | — | — | — | — | — | — | — |
| Water proof | — | — | — | — | — | — | — | — | — | — |
| Other | | | | | | | | | | |
| Operating temperature | 0~40°C | -10~50°C | 0~50°C | 0~40°C | 0~40°C | -10~50°C | -10~50°C | 0~40°C | 0~40°C | 0~40°C |
| Applicable standard | CAT.III 300V CAT.II 600V | — | — | CAT.III 300V CAT.II 600V | CAT.III 300V | CAT.III 600V | CAT.IV 600V | CAT.III 600V CAT.II 1000V | CAT.III 600V CAT.II 1000V | CAT.III 600V CAT.II 1000V |
| Power source | R6P x 1 | R6P x 1 | R6P x 2 | R03 x 2 | LR-44 x 2 | 6F22 x 1 | 6F22 x 1 | R03 x 2 | R6P x 2 | R6P x 2 |
| Dimensions (LxWxH)mm | 193 x 78 x 39 | 220 x 83 x 40 | 184 x 54 x 32 | 195 x 78 x 36 | 147 x 58.5 x 26 | 208 x 91 x 40 | 208 x 91 x 40 | 243 x 77 x 36 | 247 x 105 x 49 | 247 x 105 x 49 |
| Weight (Approx.) | 275g | 390g | 160g | 260g | 100g | 400g | 400g | 300g | 470g | 470g |

Selection Guide of Clamp Meters

| MODEL | AC/DC Clamp Meters | | | | | | | | | Fork Current Tester 2300R |
|---------------------------------|---|---|---|---|---|---|---|---|---|---|
| | 2010 | 2004 | 2033 | 2037 | 2046R | 2055 | 2056R | 2003A | 2009A | |
| Appearance |  |  |  |  |  |  |  |  |  |  |
| Display | Digital | Digital | Digital | Digital |
| Sample rate | Approx. 3 counts / sec | Approx. 3 counts / sec | Approx. 2.5 counts / sec | Approx. 3 counts / sec | 3 counts / sec | 3 counts / sec | 3 counts / sec | Approx. 2.5 counts / sec | Approx. 3 counts / sec | Approx. 2 counts / sec |
| Detection method | MEAN | MEAN | MEAN | RMS | RMS | MEAN | RMS | MEAN | RMS | RMS |
| Frequency response | DC, 40Hz~2kHz | DC, 40Hz~1kHz | DC, 20Hz~1kHz | DC, 10Hz~1kHz | DC, 40~400Hz | DC, 40~400Hz | DC, 40~400Hz | DC, 40Hz~1kHz | DC, 30Hz~1kHz | 50/60Hz |
| Conductor size (MAX.mm) | φ 7.5mm | φ 19mm | φ 24mm | φ 33mm | φ 33mm | φ 40mm | φ 40mm | φ 55mm | φ 55mm | φ 10mm |
| Measurement | | | | | | | | | | |
| AC A Resolution | 20A 0.1mA | 200A 0.01A | 300A 0.01A | 600A 0.1A | 600A 0.1A | 1000A 0.1A | 1000A 0.1A | 2000A 0.1A | 2000A 0.1A | 100A 0.1A |
| DC A Resolution | 20A 0.001A | 200A 0.01A | 300A 0.01A | 1000A 0.1A | 600A 0.1A | 1000A 0.1A | 1000A 0.1A | 2000A 0.1A | 2000A 0.1A | 100A 0.1A |
| AC V | — | 500V | — | 600V | 600V | 600V | 600V | 750V | 750V | — |
| DC V | — | 200V | — | 600V | 600V | 600V | 600V | 1000V | 1000V | — |
| Resistance | — | 200Ω | — | 4000Ω | 60MΩ | 60MΩ | 60MΩ | 4000Ω | 4000Ω | — |
| Continuity buzzer | — | — | — | ○ | ○ | ○ | ○ | ○ | ○ | — |
| Frequency | — | — | — | 3000Hz | 10kHz | 10kHz | 10kHz | — | 4000Hz | — |
| DUTY | — | — | — | — | ○ | ○ | ○ | — | — | — |
| Diod test | — | — | — | — | ○ | ○ | ○ | — | — | — |
| Capacitance test | — | — | — | — | ○ | ○ | ○ | — | — | — |
| Temperature | — | — | — | — | ○ | — | ○ | — | — | — |
| Function | | | | | | | | | | |
| NCV | — | — | — | — | ○ | ○ | ○ | — | — | ○ |
| Back light | — | — | — | — | ○ | ○ | ○ | — | — | — |
| Data hold | — | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| Peak hold | — | — | — | ○ | ○ | — | ○ | ○ | ○ | — |
| MAX/MIN | — | — | — | — | ○ | ○ | ○ | — | — | — |
| REL | — | — | — | — | ○ | ○ | ○ | — | — | — |
| Analogue output | ○(DC200mV) | — | — | — | — | — | — | ○(DC400mV) | ○(DC400mV) | — |
| Frequency filter | — | — | — | — | — | — | — | — | — | — |
| Water proof | — | — | — | — | — | — | — | — | — | — |
| Other | | | | | | | | | | |
| Operating temperature | 0~50°C | -10~50°C | 0~40°C | 0~40°C | 0~40°C | 0~40°C | 0~40°C | 0~40°C | 0~40°C | 0~40°C |
| Applicable standard | — | — | CAT. III 300V | CAT. III 600V | CAT. IV 600V | CAT. IV 600V | CAT. IV 600V | CAT. IV 600V | CAT. III 600V CAT. II 1000V | CAT. III 300V |
| Power source | 6LR61 x 1 | R6P x 2 | LR-44 x 2 | 6LR61 x 1 | R03 x 2 | R03 x 2 | R03 x 2 | R6P x 2 | 6F22 x 1 | R03 x 2 |
| Dimensions (L) x (W) x (D) [mm] | 142 x 64 x 26 [本体] 153 x 23 x 18 [センサ] | 180 x 54 x 32 | 147 x 59 x 25 | 208 x 91 x 40 | 243 x 77 x 36 | 254 x 82 x 36 | 254 x 82 x 36 | 250 x 105 x 49 | 250 x 105 x 49 | 161 x 40 x 30 |
| Weight (Approx.) | 220g | 170g | 100g | 450g | 300g | 310g | 310g | 530g | 540g | 110g |

Selection Guide of Clamp Meters

| MODEL | Leakage Clamp Meters | | | | | | | | |
|-------------------------------|---|---|---|---|---|--|---|---|---|
| | 2431 | 2432 | 2433 | 2433R | 2412 | 2434 | 2417 | 2413F | 2413R |
| Appearance |  |  |  |  |  |  |  |  |  |
| Display | Digital | Digital | Digital | Digital | Digital | Digital | Digital | Digital | Digital |
| Sample rate | 2 counts / sec | Approx. 2.5 counts / sec | Approx. 2.5 counts / sec | Approx. 2.5 counts / sec | Approx. 3 counts / sec | Approx. 2.5 counts / sec | Approx. 3 counts / sec | Approx. 3 counts / sec | Approx. 3 counts / sec |
| Detection method | MEAN | MEAN | MEAN | RMS | MEAN | MEAN | RMS | MEAN | RMS |
| Frequency response | 40~400Hz | 20Hz~1kHz | 20Hz~1kHz | 20Hz~1kHz | 40~400Hz | 40~400Hz | 40Hz~1kHz | 40Hz~1kHz | 40Hz~1kHz |
| Conductor size (MAX.mm) | φ 24mm | φ 40mm | φ 40mm | φ 40mm | φ 40mm | φ 28mm | φ 40mm | φ 68mm | φ 68mm |
| Measurement | | | | | | | | | |
| AC A Resolution | 200A 0.01mA | 100A 0.001mA | 400A 0.01mA | 400A 0.01mA | 500A 0.01mA | 100A 0.1mA | 500A 0.1mA | 1000A 0.1mA | 1000A 0.1mA |
| DC A Resolution | — | — | — | — | — | — | — | — | — |
| AC V | — | — | — | — | — | — | — | — | — |
| DC V | — | — | — | — | — | — | — | — | — |
| Resistance | — | — | — | — | — | — | — | — | — |
| Continuity buzzer | — | — | — | — | — | — | — | — | — |
| Frequency | — | — | — | — | — | — | — | — | — |
| DUTY | — | — | — | — | — | — | — | — | — |
| Dioded test | — | — | — | — | — | — | — | — | — |
| Capacitance test | — | — | — | — | — | — | — | — | — |
| Temperature | — | — | — | — | — | — | — | — | — |
| Function | | | | | | | | | |
| NCV | — | — | — | — | — | — | — | — | — |
| Back light | — | — | — | — | — | — | — | — | ○ |
| Data hold | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| Peak hold | — | ○ | ○ | ○ | — | — | ○ | ○ | ○ |
| MAX/MIN | — | — | — | — | — | — | — | — | — |
| REL | — | — | — | — | — | — | — | — | — |
| Analogue output | — | — | — | — | ○(DC200mV) | — | — | ○(DC200mV) | ○(DC200mV) |
| Frequency filter | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| Water proof | — | — | — | — | — | ○ | — | — | — |
| Other | | | | | | | | | |
| Operating temperature | 0~40°C | 0~40°C | 0~40°C | 0~40°C | 0~40°C | 0~40°C | 0~40°C | 0~40°C | 0~40°C |
| Applicable standard | CAT. III 300V | CAT. III 300V | CAT. III 300V | CAT. III 300V | — | CAT. III 300V | CAT. III 300V | CAT. III 300V | CAT. III 300V |
| Power source | LR-44 x 2 | R03 x 2 | R03 x 2 | R03 x 2 | 6F22 x 1 | R03 x 2 | 6F22 x 1 | 6F22 x 1 | 6F22 x 1 |
| Dimensions (L) x (W) x (D) mm | 147 x 59 x 25 | 185 x 81 x 32 | 185 x 81 x 32 | 185 x 81 x 32 | 209 x 96 x 45 | 169 x 75 x 40 | 209 x 96 x 45 | 250 x 130 x 50 | 250 x 130 x 50 |
| Weight (Approx.) | 100g | 290g | 270g | 270g | 450g | 220g | 450g | 570g | 600g |