

Push broach

for universal use for steel, cast metal and non-ferrous metals up to max. 35 HRC

Application:

For producing dimensionally accurate and precisely centred keyways in accordance with DIN 6885, for lever, spindle and hydraulic presses in the material groups for steel, cast iron and non-ferrous metals up to max. HRC 35 in individual part and series production.

Execution:

- precision-ground HSS, with supports

Advantage:

- high-quality cutting material, precision-ground to ensure long service life and high degree of precision
- user-friendly handling without significant set-up times



Art. no.	19205 005
Workpiece slot width	5 mm
Suitable for wedge width	5 mm
Suitable for wedge thickness	5 mm
Length	178 mm
Min./max. room length	8-43 mm
Number of openings	2 PCS
Clearing force	9.3 kN
Gross Weight	0.100 kg
Product Group	181