

Suspended wall cabinet with 2 doors with viewing window

With perforated rear wall

Application:

For stowing away tools or other parts in a clearly-arranged and space-saving manner directly on or above workstations. With perforated rear wall for accommodating RASTERPLAN tool holders and accessories.

Execution:

- Robustly welded steel sheet design
- Rear wall with square perforations 10 x 10 mm, spacing between hole centres 38 mm
- 2 holes in the rear wall for wall mounting
- 1 powder-coated shelf, height-adjustable in the grid by 17 mm, incl. 4 shelf supports, load capacity of 15 kg when load evenly distributed
- With two hinged doors
- Internal doors reinforced with box profiles, inset-type with internal pivot pins, approx. 125° door opening angle
- Lockable with cylinder lock, incl. 2 keys
- Overall load capacity of the cabinet 30 kg with evenly distributed load

Delivery:

Without fastening material



Art. no.	50045 141
Brand	PAVOY
Manufacturer Part Number	22337-080-191-735716
Door design	Inspection glass
Width	800 mm
Depth	300 mm
Height	600 mm
Number of shelves	1 PCS
Load-carrying capacity per shelf	15 kg
Back panel design	Perforated
Central locking	Yes
Lock type	Cylinder lock
Load-carrying capacity	30 kg
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Anthracite grey RAL 7016
Surface	Powder-coated
Gross Weight	21.300 kg
Product Group	5CB