

Product type designation



SCALANCE X204IRT PRO

SCALANCE X204IRT PRO, MANAGED IE IRT SWITCH IN PROT. CLASS IP65/67, 4X10/100 MBIT/S PUSH PULL RJ45 PORTS, FAULT SIGNAL CONTACT WITH SET- BUTTON, REDUNDANT POWER SUPPLY, PROFINET-IO DEVICE, NETWORK MANAGEMENT, RED.- MANAGER INTEGRATED, INCL. ELECTRONIC MANUAL ON CD, C-PLUG OPTIONAL

Transmission rate

Transfer rate	10 Mbit/s, 100 Mbit/s
---------------	-----------------------

Interfaces

Number of electrical/optical connections	
<ul style="list-style-type: none"> for network components or terminal equipment / maximum 	4
Number of electrical connections	
<ul style="list-style-type: none"> for network components or terminal equipment 	4
Type of electrical connection	
<ul style="list-style-type: none"> for network components or terminal equipment 	RJ45 push-pull plug PRO

Interfaces / for communication / integrated

Number of 100 Mbit/s SC ports / for multimode	0
Number of 1000 Mbit/s LC ports / for multimode	0

Interfaces / others

Number of electrical connections	
<ul style="list-style-type: none"> for signaling contact 	1
<ul style="list-style-type: none"> for power supply 	1
Type of electrical connection	
<ul style="list-style-type: none"> for signaling contact 	5-pin M12 socket
<ul style="list-style-type: none"> for power supply 	5-pin push-pull plug PRO socket
design of the removable storage	
<ul style="list-style-type: none"> C-PLUG 	Yes

Signal-Inputs/outputs

Operating voltage / of the signaling contacts	
<ul style="list-style-type: none"> • for DC / Rated value 	24 V
Operating current / of the signaling contacts	
<ul style="list-style-type: none"> • for DC / maximum 	0.1 A

Supply voltage, current consumption, power loss

Type of voltage / of the supply voltage	DC
Supply voltage	
<ul style="list-style-type: none"> • external 	24 V
<ul style="list-style-type: none"> • external 	18 ... 32 V
Product component / fusing at power supply input	Yes
Fuse protection type / at input for supply voltage	0.6 A / 60 V
Consumed current / maximum	0.2 A
Active power loss	
<ul style="list-style-type: none"> • for DC / at 24 V 	4.8 W

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> • during operation 	-25 ... +70 °C
<ul style="list-style-type: none"> • during storage 	-40 ... +70 °C
<ul style="list-style-type: none"> • during transport 	-40 ... +70 °C
Relative humidity	
<ul style="list-style-type: none"> • at 25 °C / without condensation / during operation / maximum 	95 %
Protection class IP	IP67

Design, dimensions and weight

Design	compact
Width	90 mm
Height	125 mm
Depth	124 mm
Net weight	1 kg
Mounting type	
<ul style="list-style-type: none"> • 35 mm DIN rail mounting 	Yes
<ul style="list-style-type: none"> • wall mounting 	Yes
<ul style="list-style-type: none"> • S7-300 rail mounting 	Yes
<ul style="list-style-type: none"> • S7-1500 rail mounting 	No

Product properties, functions, components / general

Cascading in the case of a redundant ring / at reconfiguration time of $\lt \sim 0.3 \sim$ s	100
Cascading in cases of star topology	Any (depending only on signal propagation time)

Product functions / management, configuration

Product function	
<ul style="list-style-type: none"> • CLI 	Yes

• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• Configuration with STEP 7	Yes
• Port mirroring	No
• multiport mirroring	No
• with IRT / PROFINET IO switch	Yes
• PROFINET IO diagnosis	Yes
• switch-managed	Yes

Protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	No
• DCP	Yes
• LLDP	Yes

Identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 – higher-level designation/location designation	Yes

Protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes

Product functions / Diagnosis

Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes
• Error statistics	Yes

Product functions / DHCP

Product function	
• DHCP client	Yes

Product functions / Redundancy

Product function	
• Ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes

<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with standby redundancy 	Yes
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
<ul style="list-style-type: none"> • media redundancy protocol (MRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • Passive listening 	Yes

Product functions / Security

Protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes

Product functions / Time

Product function	
<ul style="list-style-type: none"> • SICLOCK support 	Yes
Protocol / is supported	
<ul style="list-style-type: none"> • NTP 	No
<ul style="list-style-type: none"> • SNTP 	Yes

Standards, specifications, approvals

Standard	
<ul style="list-style-type: none"> • for FM 	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4
<ul style="list-style-type: none"> • for hazardous zone 	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> • for safety / from CSA and UL 	UL 60950-1, CSA C22.2 No. 60950-1
<ul style="list-style-type: none"> • for hazardous zone / from CSA and UL 	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4
<ul style="list-style-type: none"> • for emitted interference 	EN 61000-6-4:2001 (Class A)
<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-4:2001
Certificate of suitability	EN 61000-6-4:2001
<ul style="list-style-type: none"> • CE marking 	Yes
<ul style="list-style-type: none"> • C-Tick 	Yes
<ul style="list-style-type: none"> • KC approval 	Yes
<ul style="list-style-type: none"> • Railway application in accordance with EN 50155 	No
<ul style="list-style-type: none"> • Railway application in accordance with EN 50124-1 	No
Marine classification association	
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) 	No
<ul style="list-style-type: none"> • Bureau Veritas (BV) 	Yes
<ul style="list-style-type: none"> • Det Norske Veritas (DNV) 	Yes
<ul style="list-style-type: none"> • Germanische Lloyd (GL) 	Yes

<ul style="list-style-type: none"> • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS) 	<p>Yes</p> <p>Yes</p> <p>No</p>
MTBF / at 40 °C	98.55 y

Further Information / Internet Links

<p>Internet-Link</p> <ul style="list-style-type: none"> • to website: Selector SIMATIC NET SELECTION TOOL • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAx Download Manager • to website: Industry Online Support 	<p>http://www.siemens.com/snst</p> <p>http://www.siemens.com/simatic-net</p> <p>https://mall.industry.siemens.com</p> <p>http://www.siemens.com/automation/net/catalog</p> <p>http://automation.siemens.com/bilddb</p> <p>http://www.siemens.com/cax</p> <p>https://support.industry.siemens.com</p>
---	--

Security information

Security information	<p>Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit http://www.siemens.com/industrialsecurity. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit http://support.automation.siemens.com. (V3.4)</p>
----------------------	---

last modified:

16.03.2015