

Pneumatic straight grinder SRH 6-45/2

With lever valve



Application:

For fine finishing, smoothing and deburring, for powerful working.

Execution:

- Rear air exhaust

Delivery:

Includes collet chuck ZG 4/6 mm and collet chuck key size 9 + 11; in box



Art. no.	75036 055
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150010760
Model	SRH 6-45/2
Valve design	Lever valve
Max. idle speed	45000 rpm
Power output	260 W
Air consumption	380 l/min
Connection thread	R 1/8 inch
Inner hose diameter	7 mm
Length	197 mm
Diameter of housing	32 mm
Max. clamping diameter	6 mm
Collet chuck diameter	6 mm
Suitable for max. sanding block diameter	10 mm
Max. HM rotating milling cutter diameter	8 mm
Weight	0.36 kg
Gross Weight	1.000 kg
Product Group	748