

## Fittings Pneufit Push-In

Ø A = matching tube outer diameter. B = Thread (G for parallel, R for conical).  
 Drawings with complete dimensions can be found on the internet under [www.maedler.de](http://www.maedler.de)

### Straight Adaptors with Cylindrical Thread

Product No.	Ø A mm	B
860 104 03	4	M3
860 104 05	4	M5
860 104 18	4	G <sup>1/8</sup> A
860 104 28	4	G <sup>1/4</sup> A
860 106 05	6	M5
860 106 18	6	G <sup>1/8</sup> A
860 106 28	6	G <sup>1/4</sup> A
860 108 18	8	G <sup>1/8</sup> A
860 108 28	8	G <sup>1/4</sup> A
860 108 38	8	G <sup>3/8</sup> A
860 108 48	8	G <sup>1/2</sup> A
860 110 18	10	G <sup>1/8</sup> A
860 110 28	10	G <sup>1/4</sup> A
860 110 38	10	G <sup>3/8</sup> A
860 110 48	10	G <sup>1/2</sup> A
860 112 28	12	G <sup>1/4</sup> A
860 112 38	12	G <sup>3/8</sup> A
860 112 48	12	G <sup>1/2</sup> A



### Straight Unions

Product No.	Ø A mm
860 604 00	4
860 606 00	6
860 608 00	8
860 610 00	10
860 612 00	12



### Push-In Silencers

Product No.	Ø A mm
861 404 00	4
861 406 00	6
861 408 00	8



### Plugs

Product No.	Ø A mm
861 104 00	4
861 106 00	6
861 108 00	8
861 110 00	10
861 112 00	12



### Reducing / Enlarging Connectors

Product No.	Ø A1 mm	Ø A mm
860 906 04	6	4
860 908 04	8	4
860 908 06	8	6
860 910 06	10	6
860 910 08	10	8
Enlarging:		
860 904 06	4	6
860 906 08	6	8



### Pneufit Push-In Fast Connectors

- Housing made primarily from nickel-plated brass.
- Classical design.
- Operating pressure: max. 18 bar.
- Vacuum: max. -1 bar.