



AMP CT

TE Internal #: 175778-2

TE Internal Description: CT. CRIMP REC HSG 2P

AMP COMMON TERMINATION HOUSINGS

[View on TE.com >](#)



All AMP COMMON TERMINATION HOUSINGS (149)

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Also in the Series | AMP CT




PCB Connector Mounting(46)



Wire-to-Board Connector Assemblies & Housings(234)



Wire-to-Board Connector Contacts(8)



Wire-to-Board Headers & Receptacles (760)

## Customers Also Bought



TE Part #745229-5  
D-Sub Connector Contacts: Pin, Brass, Signal, Size 20



TE Part #179228-3  
AMP COMMON TERMINATION HOUSINGS



TE Part #179609-1  
AMP COMMON TERMINATION CONTACTS



TE Part #176283-1  
AMP UNIVERSA POWR CAP 3P



TE Part #103906-6  
07 MTE HDR SRRA LATCH .100CL



TE Part #1803095-3  
FLOATING SHEAR, FRONT



TE Part #1-746610-4  
16 DIP PLUG, 100CL, LEAD FREE



TE Part #1827059-3  
Std HDMI, RA, SMT

## Documents

### Product Drawings

[CT. CRIMP REC HSG 2P](#)

English

### CAD Files

[3D PDF](#)

English

Customer View Model

[ENG\\_CVM\\_175778-2\\_D1.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_175778-2\\_D1.3d\\_igs.zip](#)

English

Customer View Model



[ENG\\_CVM\\_175778-2\\_D1.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Product Specifications**

[Application Specification](#)

English

[Crimping AMP 2.0mm Pitch CT Receptacle Contact](#)

English

---

**Agency Approvals**

[CSA Certificate](#)

English