



Esselte Wet / Dry Cleaning Wipes

SAFETY DATA SHEET

13-12-2018
Revision: 1.1

ACCORDING TO EC-REGULATIONS 1907/2006 (REACH), 1272/2008 (CLP) & 2015/830

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1 Product identifier

Product Name	Esselte Wet / Dry Cleaning Wipes
Product code	67120
CAS No.	Not applicable.
EC No.	Not applicable.
REACH Registration No.	Not known.

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified Use(s)	Screen cleaner.
Uses Advised Against	Not known.

1.3 Details of the supplier of the safety data sheet

Company Identification	Acco UK Ltd. Oxford House, Oxford Road, Aylesbury, Bucks, HP21 8SZ.
Telephone	+44 (0) 844 209 8360
Fax	+44 (0) 845 603 1731
E-mail	informationeurope@acco.com
Website	www.acco.co.uk
Office hours	09:00 - 17:00

1.4 Emergency telephone number

Company	+44 (0) 844 209 8360 (09:00 - 17:00)
National Poisons Information Service (NHS Direct)	111 (England & Wales only) or 112 (EU) or 08454 24 24 24 (Scotland)

SECTION 2: HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

Regulation (EC) No. 1272/2008 (CLP)	Not classified as dangerous for supply/use.
-------------------------------------	---

2.2 Label elements

	According to Regulation (EC) No. 1272/2008 (CLP)
Product Name	Esselte Wet / Dry Cleaning Wipes
Hazard Pictogram(s)	None.
Signal Word(s)	None.
Hazard Statement(s)	EUH208: Contains: Benzisothiazolinone. May produce an allergic reaction.
Precautionary Statement(s)	None.

2.3 Other hazards

None known.

2.4 Additional Information

None.



SAFETY DATA SHEET

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1 Substances

Not applicable.

3.2 Mixtures

HAZARDOUS INGREDIENT(S)	CAS No.	EC No. / REACH Registration No.	%W/W	Hazard Statement(s)	Hazard Pictogram(s)
(2-methoxymethylethoxy) propanol	34590-94-8	252-104-2 01-2119450011-60-XXXX	5-15	Not classified	None
Benzisothiazolinone	2634-33-5	220-120-9 01-2120761540-60-XXXX	<0.05	Acute Tox. 4 H302 Skin Irrit. 2 H315 Skin Sens. 1 H317 Eye Dam. 1 H318 Aquatic Acute 1 H400	GHS05 GHS09

SECTION 4: FIRST AID MEASURES

4.1 Description of first aid measures

Inhalation	If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing.
Skin Contact	Wash skin with water.
Eye Contact	Flush eyes with water for at least 15 minutes.
Ingestion	Wash out mouth with water.

4.2 Most important symptoms and effects, both acute and delayed

None anticipated.

4.3 Indication of any immediate medical attention and special treatment needed

Unlikely to be required but if necessary treat symptomatically.

SECTION 5: FIREFIGHTING MEASURES

5.1 Extinguishing media

Suitable Extinguishing media	As appropriate for surrounding fire.
Unsuitable extinguishing media	None.

5.2 Special hazards arising from the substance or mixture

Decomposes in a fire giving off toxic fumes: Carbon monoxide, Carbon dioxide

5.3 Advice for firefighters

Fire fighters should wear complete protective clothing including self-contained breathing apparatus.



SAFETY DATA SHEET

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures

Provide adequate ventilation when using the material and follow the principles of good occupational hygiene to control personal exposures. Wear suitable gloves if prolonged skin contact is likely.

6.2 Environmental precautions

Do not release large quantities into the surface water or into drains.

6.3 Methods and material for containment and cleaning up

Adsorb spillages onto sand, earth or any suitable adsorbent material. Transfer to a container for disposal or recovery.

6.4 Reference to other sections

See Also Section 8, 13.

SECTION 7: HANDLING AND STORAGE

7.1 Precautions for safe handling

General hygiene measures for the handling of chemicals are applicable. Wear protective equipment to comply with good occupational hygiene practice. Wash hands and exposed skin after use. Do not eat, drink or smoke at the work place.

7.2 Conditions for safe storage, including any incompatibilities

Keep container tightly closed and dry.

Storage temperature

0-35°C

Storage life

24 Month(s).

Incompatible materials

None known.

7.3 Specific end use(s)

Screen cleaner.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 Control parameters

8.1.1 Occupational Exposure Limits

SUBSTANCE	CAS No.	LTEL (8 hr TWA ppm)	LTEL (8 hr TWA mg/m ³)	STEL (ppm)	STEL (mg/m ³)	Note
(2-methoxymethylethoxy) propanol	34590-94-8	50	308			Sk
(2-methoxymethylethoxy) propanol	34590-94-8	50	308	0	0	IOELV, Skin

Region

Source

EU

EU Occupational Exposure Limits

United Kingdom

UK Workplace Exposure Limits EH40/2005 (Third edition, published 2018)

SAFETY DATA SHEET

Remark	Notes
Sk	Can be absorbed through the skin. The assigned substances are those for which there are concerns that dermal absorption will lead to systemic toxicity.
IOELV	Indicative Occupational Exposure Limit Value.
Skin	The possibility of significant uptake through the skin.

8.2 Exposure controls

8.2.1. Appropriate engineering controls Ensure adequate ventilation.

8.2.2. Personal protection equipment



Eye Protection Not normally required. Wear protective eye glasses for protection against liquid splashes.



Skin protection Not normally required. Wear suitable gloves if prolonged skin contact is likely.



Respiratory protection Normally no personal respiratory protection is necessary.



Thermal hazards Not applicable.

8.2.3. Environmental Exposure Controls Do not release large quantities into the surface water or into drains.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1 Information on basic physical and chemical properties

Appearance	Liquid.
	Colour : Colourless.
Odour	Almost odourless.
Odour threshold	Not established.
pH	~8
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not available.
Flash Point	>100°C
Evaporation rate	Not available.
Flammability (solid, gas)	Not applicable.
Upper/lower flammability or explosive limits	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	~1 g/ml
Solubility(ies)	Solubility (Water) : Completely soluble in water. Solubility (Other) : Not known.
Partition coefficient: n-octanol/water	Not available.



Esselte Wet / Dry Cleaning Wipes

13-12-2018
Revision: 1.1

SAFETY DATA SHEET

Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	Not available.
Explosive properties	Not explosive.
Oxidising properties	Not oxidising.

9.2 Other information

None.

SECTION 10: STABILITY AND REACTIVITY

10.1 Reactivity

Stable under normal conditions.

10.2 Chemical Stability

Stable under normal conditions.

10.3 Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose.

10.4 Conditions to avoid

None anticipated.

10.5 Incompatible materials

None known.

10.6 Hazardous decomposition products

No hazardous decomposition products known.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1 Information on toxicological effects

Acute toxicity	Low acute toxicity.
Skin corrosion/irritation	Non-irritant.
Serious eye damage/irritation	Non-irritant.
Skin sensitization data	It is not a skin sensitiser.
Respiratory sensitization data	Not classified.
Germ cell mutagenicity	There is no evidence of mutagenic potential.
Carcinogenicity	No evidence of carcinogenicity.
Reproductive toxicity	No evidence of reproductive effects.
Lactation	Not classified.
STOT - single exposure	None anticipated.
STOT - repeated exposure	None anticipated.
Aspiration hazard	Not classified.

11.2 Other information

Not known.



Esselte Wet / Dry Cleaning Wipes

SAFETY DATA SHEET

13-12-2018
Revision: 1.1

SECTION 12: ECOLOGICAL INFORMATION

12.1 Toxicity

Low toxicity to aquatic organisms.

12.2 Persistence and Degradation

The product is biodegradable. Unlikely to persist.

12.3 Bioaccumulative potential

The product has no potential for bioaccumulation.

12.4 Mobility in soil

Soluble in water. The product is predicted to have high mobility in soil.

12.5 Results of PBT and vPvB assessment

Not classified as PBT or vPvB.

12.6 Other adverse effects

Not known.

SECTION 13: DISPOSAL CONSIDERATIONS

13.1 Waste treatment methods

Dispose of empty containers and wastes safely. Dispose at suitable refuse site.

13.2 Additional Information

Disposal should be in accordance with local, state or national legislation.
Waste code: 07 06 wastes from the MFSU of fats, grease, soaps, detergents, disinfectants and cosmetics

SECTION 14: TRANSPORT INFORMATION

Not classified as dangerous for transport.

14.1 UN number

Not applicable.

14.2 UN proper shipping name

Not applicable.

14.3 Transport hazard class(es)

Not applicable.

14.4 Packing group

Not applicable.

14.5 Environmental hazards

Not classified as a Marine Pollutant.

14.6 Special precautions for user

Not applicable.

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable.



Esselte Wet / Dry Cleaning Wipes

SAFETY DATA SHEET

13-12-2018
Revision: 1.1

SECTION 15: REGULATORY INFORMATION

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

European Regulations - Authorisations and/or Restrictions On Use

Candidate List of Substances of Very High Concern for Authorisation Not listed.

REACH: ANNEX XIV list of substances subject to authorisation Not listed.

REACH: Annex XVII Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles Not listed.

Community Rolling Action Plan (CoRAP) Not listed.

Other Not known.

National regulations

Other Not known.

15.2 Chemical Safety Assessment

Not available.

SECTION 16: OTHER INFORMATION

The following sections contain revisions or new statements: 1-16

LEGEND

Hazard Pictogram(s)	GHS05: GHS: corrosive GHS09: GHS: fish and tree
Hazard classification	Acute Tox. 4 : Acute toxicity, Category 4 Aquatic Acute 1 : Hazardous to the aquatic environment, Acute, Category 1 Eye Dam. 1 : Serious eye damage/irritation, Category 1 Skin Irrit. 2 : Skin corrosion/irritation, Category 2 Skin Sens. 1 : Skin sensitization, Category 1
Hazard Statement(s)	H302: Harmful if swallowed. H315: Causes skin irritation. H317: May cause an allergic skin reaction. H318: Causes serious eye damage. H400: Very toxic to aquatic life.
Acronyms	CAS : Chemical Abstracts Service CLP : Regulation (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures EC : European Community EINECS : European Inventory of Existing Commercial Chemical Substances LTEL : Long term exposure limit PBT : Persistent, Bioaccumulative and Toxic REACH : Registration, Evaluation, Authorisation and Restriction of Chemicals



Esselte Wet / Dry Cleaning Wipes

SAFETY DATA SHEET

13-12-2018
Revision: 1.1

STEL : Short term exposure limit
STOT : Specific Target Organ Toxicity
vPvB : very Persistent and very Bioaccumulative

Disclaimers

Information contained in this publication or as otherwise supplied to Users is believed to be accurate and is given in good faith, but it is for the Users to satisfy themselves of the suitability of the product for their own particular purpose.

Acco UK Ltd. gives no warranty as to the fitness of the product for any particular purpose and any implied warranty or condition (statutory or otherwise) is excluded except to the extent that exclusion is prevented by law.

Acco UK Ltd. accepts no liability for loss or damage (other than that arising from death or personal injury caused by defective product, if proved), resulting from reliance on this information. Freedom under Patents, Copyright and Designs cannot be assumed.