

CRIMP Ratchet Tool for 0.093" Terminals, 24-14 AWG, with Locator

This tool is designed for double crimp terminals.


W-HTR-1031-E

UPC: 010151191250

HTS: 8203.20.6060

Weight: 15 oz.
Overall Length: 9"

Closed Width ~ 2.25"



The conductor and insulation crimps are "B" type which are produced in two cavities: 24-20 AWG and 18-14 AWG.

A locator and wire stop are provided to orient the pins or sockets during crimping.

with Locator

Locator & Wire Stop to Position Contacts

Two Cavities : (24 - 20) AWG and (18 - 14) AWG

P/N #	Series #
02-09-1104	1189
02-09-1102	1189
02-09-2103	1190
02-09-2101	1190
02-09-2118	1380
02-09-2116	1380
02-09-6123	1380
02-09-1119	1381
02-09-1117	1381
02-09-5142	1381

P/N #	Series #
02-08-1102	1881
02-08-1101	1881
02-09-8103	1973
02-09-8108	1973
02-09-2166	4549
02-09-1205	4550

Nest Cavity	Conductor
A	(0.049 / 0.045)"
B	(0.053 / 0.047)"



Ratchet Controlled Release
Ratchet Set to Release when at (55-65) lb.s